



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LAMA2014QY 1BRL Alcu Lug

Panduit Corporation

|                  |  |
|------------------|--|
| Catalog Number   | LAMA2014QY   |
| Manufacturer     | Panduit Corporation  |
| Description      | Single Barrel Lug, #14 Awg Conductor Size, 2/0 Awg Conductor Size, Non-Insulated, Copper Conductor Material, +90 °C Operating Temperature, 1.47 In Overall Length, Screw Terminal, 600 V |
| Weight per unit  | 0.9700 (lbs/each)  |
| Product Category | Large Terminals & Connectors   |

### Features

|                 |               |
|-----------------|---------------|
| amperage rating | NA            |
| insulation      | Non-Insulated |
| Material        | Aluminum      |
| media           | Yes           |
| Number of Holes | 1             |
| Stud Size       | 1/4           |
| Voltage Rating  | 600           |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 1BRL ALCU LUG                       |
| extra long description | PAN LAMA2/0-14-QY Pan-Lug™ LAMA2/0- |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983596119 |
| UPC   | 074983596119   |

### Taxonomies, Classifications, and Categories

|                      |                |
|----------------------|----------------|
| Category Description | SPLIT BOLTS    |
| Type                 | Mechanical Lug |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 50   |
| Weight Per each | 0.97 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Stranded Aluminum or Copper Code Conductor                  |
| Mounting    | 0.62  |
| standard    | cULus Listed for use up to 600V & Temperature Rated to 90°C |