



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



K4421M 120V Metal Stem Photocontrol 120V

Intermatic Inc.

Catalog Number	K4421M
Manufacturer	Intermatic Inc.
Description	Metal Stem Mount Thermal Photocontrol, 120 V
Weight per unit	0.2510 (lbs/each)
Product Category	Lighting Photocells

Features

connection	Color Coded Lead
Connection Type	1/2 IN - 14 NPT Thread
supply voltage	120

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	1-15/16 LENGTH X 1-15/16 WIDTH X 3-3/4 DEPTH IN, 4.9 LENGTH X 4.9 WIDTH X 9.5 DEPTH CM
------	--

Descriptions

Description	120V METAL STEM PHOTOCONTROL 120V
extra long description	INT-MAT K4421M Metal Stem Mount The
Features	These photocontrols install on standard outdoor light fixtures and electrical boxes with 1 2"-14 NPSM thread or 7 8" knock-out holes for dusk-to-dawn ON/OFF control of outdoor lighting.
Long Description	Metal Stem Mount Thermal Photocontrol, 120 V
Product Type	Metal Stem Mount Thermal Photocontrol, 120 V
Special Features	Features: Cadmium Sulfide Photocell, Sonic-Welded Polycarbonate Housing, 6 IN Wire Leads, Light Level Slide Adjustment

Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275105997
Manufacturers Part Number	K4421M
UPC	078275105997

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Thermal Type Photo Cell

Packaging

Carton	1
Package	12
Weight Per each	0.251



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Dusk to Dawn Lighting Control
Frequency Rating	50/60
Mounting	Stem Mount
Operating Temperature standard	-40 to +158 DEG F -40 to +70 DEG C UL Recognized, CSA, C/UL Recognized, Title CA 20 Listed, California Title 24 Compliant