



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED10RS6830E26P1 10W 6" Led Rec DWNLT 30K

Ge By Current Lamps

| | |
|------------------|---|
| Catalog Number | LED10RS6830E26P1 |
| Manufacturer | Ge By Current Lamps |
| Description | Recessed Downlight Fixture, 7.5 Inch Lamp Length; UL (Canada and Us) Approval; 1 Lamp(S); Led Recessed Downlight; Led Lamp Type; 10 W Lamp Wattage; 120 V Input Voltage; 50000 Life In Hour; 700 Lumen Intensity; 120 V Lamp Voltage; E26 Lamp Base |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Led Recessed Architectural & S |

Features

| | |
|---------------------|------------------------|
| area classification | Damp Location |
| Input Voltage | 120 V |
| Intensity | 700 LUMEN |
| Item | LED Recessed Downlight |
| Lamp Base | E26 |
| Lamp Length | 7.5 Inch |
| Lamp Type | LED |
| Lamp Voltage | 120 V |
| Lamp Wattage | 10 W |
| Number of Lamps | 1 PH |

Descriptions

| | |
|------------------------|---|
| Additional Information | Recessed Can Size 6 Inch; Color Temperature 3000 K; Color Rendering Index 80 |
| Commodity Description | LED RECESSED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Description | 10W 6" LED REC DWNLT 30K |
| Long Description | RECESSED DOWNLIGHT FIXTURE, 7.5 INCH LAMP LENGTH; UL (CANADA AND US) APPROVAL; 1 LAMP(S); LED RECESSED DOWNLIGHT; LED LAMP TYPE; 10 W LAMP WATTAGE; 120 V INPUT VOLTAGE; 50000 LIFE IN HOUR; 700 LUMEN INTENSITY; 120 V LAMP VOLTAGE; E26 LAMP BASE |
| Product Type | Recessed Downlight Fixture |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | GE LIGHTING, INC./LAMPS |
| GTIN | 00043168851602 |
| Manufacturers Part Number | LED10RS6830E26P120 |
| UPC | 043168851602 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | LED GENERAL PURPOSE LIGHTING |
|----------------------|------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging


| | |
|-----------------|-----|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards



| | |
|----------|--------------------|
| Approval | UL (CANADA AND US) |
|----------|--------------------|

LED replacement lamps

LED HID

| Bulb Shape | Base Type | Watts | Order Code | Description | Volts | Case Qty** | MOL (In) | Lumens Initial | CBCP | Initial Color Temp | CRI | Wattage Replacement | *Rated Life L70 (Hrs) | Dimmable | ENERGY STAR® Status | #Location Rating | Additional Information | |
|--|-----------|-------|------------|-----------------|-------|------------|----------|----------------|------|--------------------|-----|---------------------|-----------------------|----------|---------------------|------------------|---|--|
| 400 Watt Metal Halide Replacement Lamp | | | | | | | | | | | | | | | | | | |
|  | EX39 | 165 | 21259 | LED165/M400/740 | | 3 | 11.42 | 20,000 | | 4000 | 73 | 400 | 50,000 | - | | Dry | Open Rated, CWA, ANSI - M59, M135, M155 | |

Plug-In


| Bulb Shape | Base Type | Watts | Order Code | Description | Volts | Case Qty** | MOL (In) | Lumens Initial | CBCP | Initial Color Temp | CRI | Wattage Replacement | *Rated Life L70 (Hrs) | Dimmable | #Location Rating | Additional Information | |
|--|-----------|-------|------------|-----------------|-------|------------|----------|----------------|------|--------------------|-----|---------------------|-----------------------|----------|------------------|------------------------------------|--|
| Vertical | | | | | | | | | | | | | | | | | |
|  | G24q/GX24 | 12 | 96801 | LED12G24Q-V/827 | # | 6 | 5.31 | 950 | | 2700 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96775 | LED12G24Q-V/830 | # | 6 | 5.31 | 950 | | 3000 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96689 | LED12G24Q-V/835 | # | 6 | 5.31 | 1000 | | 3500 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96771 | LED12G24Q-V/840 | # | 6 | 5.31 | 1000 | | 4000 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| Horizontal | | | | | | | | | | | | | | | | | |
|  | G24q/GX24 | 12 | 96799 | LED12G24Q-H/827 | # | 6 | 5.31 | 950 | | 2700 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96798 | LED12G24Q-H/830 | # | 6 | 5.31 | 950 | | 3000 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96761 | LED12G24Q-H/835 | # | 6 | 5.31 | 1000 | | 3500 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 96769 | LED12G24Q-H/840 | # | 6 | 5.31 | 1000 | | 4000 | 80 | | 50000 | - | Damp | Requires Electronic Ballast, White | |

- Check compatibility at GELighting.com/LED4pin-compatibility

High Lumen Biax

| Bulb Shape | Base Type | Watts | Order Code | Description | Volts | Case Qty** | MOL (In) | Lumens Initial | CBCP | Initial Color Temp | CRI | Wattage Replacement | *Rated Life L70 (Hrs) | Dimmable | #Location Rating | Additional Information | |
|-------------------------------|-----------|-------|------------|------------------|-------|------------|----------|----------------|------|--------------------|-----|---------------------|-----------------------|----------|------------------|------------------------------------|--|
| High Lumen Biax (HLBX) | | | | | | | | | | | | | | | | | |
| HLBX | 2G11 | 17 | 39073 | LED172G11/830/10 | # | 10 | | 2100 | | 3000 | 80 | | 40000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 39074 | LED172G11/835/10 | # | 10 | | 2100 | | 3500 | 80 | | 40000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 39075 | LED172G11/840/10 | # | 10 | | 2150 | | 4000 | 80 | | 40000 | - | Damp | Requires Electronic Ballast, White | |
| | | | 39076 | LED172G11/850/10 | # | 10 | | 2150 | | 5000 | 80 | | 40000 | - | Damp | Requires Electronic Ballast, White | |

RS Cans

| Bulb Shape | Base Type | Watts | Order Code | Description | Volts | Case Qty** | MOL (In) | Lumens Initial | CBCP | Initial Color Temp | CRI | Wattage Replacement | *Rated Life L70 (Hrs) | Dimmable | ENERGY STAR® Status | #Location Rating | Additional Information |
|--|-----------|-------|------------|------------------|-------|------------|----------|----------------|------|--------------------|-----|---------------------|-----------------------|----------|---------------------|------------------|----------------------------|
| RS Cans | | | | | | | | | | | | | | | | | |
|  | E26 | 10 | 95853 | LED10RS4/827E26P | 120 | 12 | 5.88 | 700 | | 2700 | 80 | 65W | 50,000 | Yes | ★ | Damp | 4" Can, Pigtail Attachment |
| | | | 95854 | LED10RS4/830E26P | 120 | 12 | 5.88 | 700 | | 3000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 4" Can, Pigtail Attachment |
| | GU24 | | 95855 | LED10RS4/827GUP | 120 | 12 | 5.88 | 700 | | 2700 | 80 | 65W | 50,000 | Yes | ★ | Damp | 4" Can, Pigtail Attachment |
| | | | 95856 | LED10RS4/830GUP | 120 | 12 | 5.88 | 700 | | 3000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 4" Can, Pigtail Attachment |
| | E26 | | 85153 | LED10RS6/827E26P | 120 | 12 | 7.5 | 700 | | 2700 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 85160 | LED10RS6/830E26P | 120 | 12 | 7.5 | 700 | | 3000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 30367 | LED10RS6/840E26P | 120 | 12 | 7.5 | 700 | | 4000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 35365 | LED10RS4/840E26P | 120 | 12 | 7.5 | 700 | | 4000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | GU24 | | 95851 | LED10RS6/827GUP | 120 | 12 | 7.5 | 700 | | 2700 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 95852 | LED10RS6/830GUP | 120 | 12 | 7.5 | 700 | | 3000 | 80 | 65W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | E26 | 13 | 70120 | LED13RS6/827E26P | 120 | 12 | 7.5 | 1000 | | 2700 | 80 | 90W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 70122 | LED13RS6/830E26P | 120 | 12 | 7.5 | 1000 | | 3000 | 80 | 90W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | GU24 | | 70124 | LED13RS6/827GUP | 120 | 12 | 7.5 | 1000 | | 2700 | 80 | 90W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |
| | | | 70127 | LED13RS6/830GUP | 120 | 12 | 7.5 | 1000 | | 3000 | 80 | 90W | 50,000 | Yes | ★ | Damp | 6" Can, Pigtail Attachment |

Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display. 2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at
GELighting.com/ThinkLED