

LED Replacement Lamps

LED PAR30 Short, Long Neck and High Output Directional Lamps



Project Name _____

Date _____ Type _____

Notes _____

For the perfect solution for all of your retail application needs, turn to Current's retail PAR30 short and long neck lamps. With advanced optics and reduced glare, these lamps offer the light qualities desired by merchants.

PERFORMANCE HIGHLIGHTS:

PAR30 Lamps	
Light Output Range:	850-1800 Lumens
CRI:	80 & 90
CCT:	2700K & 3000K
Input Voltage:	120-277
Efficiency:	Up to 100 LPW
Wattage:	12W & 18W
Life:	25,000 hours L70
Temperature Rating:	-20°C to 45°C
Rating:	Damp

LIMITED WARRANTY

3 Years

FEATURES:

- Halogen-like color
- Available in different beam patterns
- These lamps are energy efficient, contain no lead or mercury

BENEFITS:

Energy + Cost Savings

- For example, using only 12 watts of energy, save over \$173 in energy costs over the rated life of the lamp versus a standard 75-watt halogen PAR30 lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources
- Our LED PAR lamps have less heat, UV or infrared in the beam, which reduces the potential for fading of materials and décor, compared to halogen or incandescent lamps



Featuring Current's exclusive Visual Comfort Lens for the perfect blend of enhanced color quality, advanced optics and reduced glare. Exclusive Visual Comfort Lens Optics create halogen-like light and contrast, with the energy and cost-efficient benefits of an LED lamp.

LEARN MORE:

To learn more about saving money and energy, go to

www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LED Replacement Lamps

LED PAR30 Short, Long Neck and High Output Directional Lamps

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Directional Lamps (PAR30 - Low Glare - Visual Comfort Lens™)

Base Type	Order Type	Watts	Code	Description	Case Volts	MOL Qty**	Lumens (ln)	Initial CBCP	Initial Temp	Color CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	# Location Rating	Additional Information	
Compact PAR30 - Low Glare - Visual Comfort Lens™																	
PAR30	E26	12	84379	LED12DP30RW93025	120	6	3.74	900	3900	3000	90	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	84380	LED12DP30RW93040	120	6	3.74	900	1800	3000	90	75	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	84392	LED12DP30RW92725	120	6	3.74	850	3500	2700	90	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	93107784	LED12DP30RB927/40	120	6	3.74	850	1700	2700	90	50	25,000	Yes	–	Damp	Flood, 40° beam, Black Casing
	E26	12	84395	LED12DP30RW92740	120	6	3.74	850	1700	2700	90	75	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	84384	LED12DP30RW83025	120	6	3.74	1050	4800	3000	80	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	42131	LED12DP30RW83040	120	6	3.74	1050	2400	3000	80	75	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	42133	LED12DP30RW82725	120	6	3.74	1000	4700	2700	80	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	42134	LED12DP30RW82740	120	6	3.74	1000	2200	2700	80	75	25,000	Yes	★	Damp	Flood, 40° beam, White
E26	12	73583	LED12DP30RB82740	120	6	3.74	1000	2200	2700	80	75	25,000	Yes	★	Damp	Flood, 40° beam, Black	
Compact PAR30 - Long Neck - Low Glare - Visual Comfort Lens																	
PAR30	E26	12	84399	LED12DP3LRW93025	120	6	4.72	900	3900	3000	90	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	84400	LED12DP3LRW93040	120	6	4.72	900	1800	3000	90	75	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	84407	LED12DP3LRW92740	120	6	4.72	850	1700	2700	90	75	25,000	Yes	–	Damp	Flood, 40° beam, White
	E26	12	42136	LED12DP3LRW83025	120	6	4.72	1050	4800	3000	80	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	42137	LED12DP3LRW83040	120	6	4.72	1050	2400	3000	80	75	25,000	Yes	★	Damp	Flood, 40° beam, White
	E26	12	42141	LED12DP3LRW82725	120	6	4.72	1000	4700	2700	80	75	25,000	Yes	★	Damp	Narrow Flood, 25° beam, White
	E26	12	42144	LED12DP3LRW82740	120	6	4.72	1000	2200	2700	80	75	25,000	Yes	★	Damp	Flood, 40° beam, White

Directional Lamps (PAR30 - STIR)

Compact PAR30																	
PAR30	E26	12	98755	LED12DP303W83035	120	6	3.66	950	2600	3000	80	75	25,000	Yes	★	Damp	Flood, 35° beam, White, STIR
Compact PAR30 Long Neck																	
PAR30L	E26	12	98811	LED12DP3L3W83035	120	6	4.61	950	2600	3000	80	75	25,000	Yes	★	Damp	Accent, 35° beam, White, STIR

Directional Lamps (PAR30 - High Output)

Universal 120-277V																	
PAR30 HO	E26	18	75089	LED18P30LW83015	120-277	6	4.6	1800	15500	3000	80	75	25,000	Yes	–	Damp	Spot, 15°, White
	E26	18	75091	LED18P30LW83025	120-277	6	4.6	1800	7000	3000	80	75	25,000	Yes	–	Damp	Narrow Flood, 25°, White
	E26	18	75065	LED18P30LW93015	120-277	6	4.6	1400	12500	3000	90	75	25,000	Yes	–	Damp	Spot, 15° beam, MTO, 1000 Min. Qty, 12 Week Lead Time, White
	E26	18	75078	LED18P30LW93025	120-277	6	4.6	1400	5000	3000	90	75	25,000	Yes	–	Damp	Narrow Flood, 25°, White

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a "★" are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.