

Integrated LED Tubes

Type A T8 Glass Tubes

Project Name _____

Date _____ Type _____

Notes _____

Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall. LED tubes are ideal for those seeking high energy savings with minimal installation time. Each LED tube is outfitted with an internal driver. The Type A LED tubes run on either a electronic T8 instant-start or programmed start ballast.



PERFORMANCE HIGHLIGHTS:

Type A T8 Glass Tubes	
Light Output Range:	1300-2100 Lumens
CRI:	80+
CCT:	3000K-6500K
Wattage:	8-18W
Life:	70,000 hours L70
Temperature Rating:	-20°C to 40°C
Rating:	Damp
Fixtures:	Open or Enclosed
Dimming:	Dimmable with compatible dimming ballasts
Ballast Compatability Guide:	gecurrent.com/LEDTUBES-ballastcompatibility
Certification:	DLC Listed

BENEFITS:

- Fast and easy LED upgrade
- Low energy LFL replacement
- 2.3X Longer Life vs LFL (70,000 vs. 30,000 hours)
- Better quality of life-instant on
- Easy disposal, non-hazardous waste

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LIMITED WARRANTY

7 Years

Integrated LED Tubes

Type A T8 Glass Tubes

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Type	Base Type	Order Code	Description	NBF Lamp Watts	NBF System Watts	Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	*Rated Life L70 (Hrs)	DLC®	UL	# Location Rating	Additional Information
Integrated 4 ft LED Glass Tubes (operates on Instant Start or Program Start Ballast)															
T8	G13	35767	LED18ET8/G/4/830	18	20	20	48	2500	3000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35768	LED18ET8/G/4/835	18	20	20	48	2500	3500K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35769	LED18ET8/G/4/840	18	20	20	48	2500	4000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35772	LED18ET8/G/4/850	18	20	20	48	2600	5000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35773	LED18ET8/G/4/865	18	20	20	48	2600	6500K	80+	70,000	-	Yes	Damp	Instant or PRS Ballast
	G13	35790	LED15ET8/G/4/830	15	17	20	48	2150	3000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35791	LED15ET8/G/4/835	15	17	20	48	2200	3500K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35793	LED15ET8/G/4/840	15	17	20	48	2200	4000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35797	LED15ET8/G/4/850	15	17	20	48	2300	5000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35798	LED15ET8/G/4/865	15	17	20	48	2300	6500K	80+	70,000	-	Yes	Damp	Instant or PRS Ballast
	G13	34277	LED10ET8/G/4/830	10	12.5	20	48	1600	3000K	80+	70,000	-	Yes	Damp	Instant or PRS Ballast
	G13	34279	LED10ET8/G/4/835	10	12.5	20	48	1600	3500K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	34280	LED10ET8/G/4/840	10	12.5	20	48	1700	4000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
G13	34282	LED10ET8/G/4/850	10	12.5	20	48	1700	5000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast	
Integrated 3 ft LED Glass Tubes (operates on Instant Start or Program Start Ballast)															
T8	G13	35783	LED11ET8/G/3/830	10.5	13	20	36	1600	3000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35784	LED11ET8/G/3/835	10.5	13	20	36	1600	3500K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35788	LED11ET8/G/3/840	10.5	13	20	36	1600	4000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35789	LED11ET8/G/3/850	10.5	13	20	36	1650	5000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
Integrated 2 ft LED Glass Tubes (operates on Instant Start or Program Start Ballast)															
T8	G13	35775	LED8ET8/G/2/830	8.5	11	20	24	1350	3000K	80+	70,000	-	Yes	Damp	Instant or PRS Ballast
	G13	35776	LED8ET8/G/2/835	8.5	11	20	24	1350	3500K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35778	LED8ET8/G/2/840	8.5	11	20	24	1350	4000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	35779	LED8ET8/G/2/850	8.5	11	20	24	1400	5000K	80+	70,000	Yes	Yes	Damp	Instant or PRS Ballast

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.