




GE
Lighting

68182 - LED26DP38S840/40

GE LED PAR38

- Energy-efficient LED lamps. Long life.



GENERAL CHARACTERISTICS

Lamp Type	Replacement Lamps - Directional
Bulb	PAR38
Base	Medium Screw (E26)
Bulb Shape	PAR38
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	100.0 W
Lamp Type	LED-PAR
Life in Years (NOM)	22.8
Rated Life (MIN)	25000.0 h
Rated Life (NOM)	25000.0 h

PHOTOMETRIC CHARACTERISTICS

Beam Spread (NOM)	40.0 °
Center Beam Candlepower (CBCP) (NOM)	3200.0
Color Rendering Index (CRI) (NOM)	82.0
Color Temperature (NOM)	4000.0 K
Initial Lumens (TYP)	1650.0
Initial Lumens (NOM)	1650.0
Lumens per Watt (Efficacy) (NOM)	63.0 lm
Nominal Initial Lumens per Watt (NOM)	63.46154

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year (NOM)	3.13
Voltage (NOM)	120.0
Wattage (NOM)	26.0

DIMENSIONS

Bulb Diameter (DIA) (MIN)	4.750 in(120.6 mm)
Bulb Diameter (DIA) (NOM)	4.750 in(120.6 mm)
Maximum Overall Length (MOL) (NOM)	5.310 in(134.9 mm)

PRODUCT INFORMATION

Product Code	68182
Description	LED26DP38S840/40
Standard Package	00-Case
Standard Package GTIN	10043168681824
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168681827