








GE energy smart® LED replacement lamps

Decorative Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information			
Candles																				
	MED	1.8	62988	LED2CAM-F/ES/TP	120	3	4.5	75		3000	80	10W	15,000	-	★	Dry	Frost, Bent tip			
			62989	LED2CAM-C/ES/TP	120	3	4.5	75		3000	80	10W	15,000	-	★	Dry	Clear, Bent tip			
		2	76453	LED2CAM/W/TP	120	3	4.5	60		2900	82	-	12,000	-	-	-	Dry	Frost, Bent tip		
			76454	LED2CAM/C/TP	120	3	4.5	60		2900	82	-	12,000	-	-	-	Dry	Clear, Bent tip		
		2.2	64047	LED2DCAM-F	120	48**	4.5	90		3000	80	15W	15,000	Yes	★	Damp	Frost, Bent tip			
			64048	LED2DCAM-C	120	48**	4.5	90		3000	80	15W	15,000	Yes	★	Damp	Clear, Bent tip			
			67994	LED2DCAM-F/827	120	48**	4.5	90		2700	80	15W	15,000	Yes	★	Damp	Frost, Bent tip			
			67995	LED2DCAM-C/827	120	48**	4.5	90		2700	80	15W	15,000	Yes	★	Damp	Clear, Bent tip			
			3.5	68168	LED3DCAM-C/TP	120	3	4.2	170		2700	80	25W	15,000	Yes	★	Damp	Clear, Bent Tip		
				68167	LED4DCAM-F/TP	120	3	4.2	270		2700	82	25W	15,000	Yes	★	Damp	Frost, Blunt Tip		
	CAND	1.8	61544	LED2CAC-F/ES/TP	120	3	4.1	75		3000	80	10W	15,000	-	★	Dry	Frost, Bent tip			
			61545	LED2CAC-C/ES/TP	120	3	4.1	75		3000	80	10W	15,000	-	★	Dry	Clear, Bent tip			
		2	76455	LED2CAC/W/TP	120	3	4.1	60		2900	82	-	12,000	-	-	-	Dry	Frost, Bent tip		
			78822	LED2CAC/W	120	48**	4.1	60		2900	82	-	12,000	-	-	-	Dry	Frost, Bent tip		
		2.2	76456	LED2CAC/C/TP	120	3	4.1	60		2900	82	-	12,000	-	-	-	Dry	Clear, Bent tip		
			78823	LED2CAC/CLR	120	48**	4.1	60		2900	82	-	12,000	-	-	-	Dry	Clear, Bent tip		
		3.5	64045	LED2DCAC-F	120	48**	4.3	90		3000	80	15W	15,000	Yes	★	Damp	Frost, Bent tip			
			67992	LED2DCAC-F/827	120	48**	4.3	90		2700	80	15W	15,000	Yes	★	Damp	Frost, Bent tip			
			67993	LED2DCAC-C/827	120	48**	4.3	90		2700	80	15W	15,000	Yes	★	Damp	Clear, Bent tip			
			68166	LED3DCAC-C/TP	120	3	4.3	170		2700	80	25W	15,000	Yes	★	Damp	Clear, Bent Tip			
4.5	68165	LED4DCAC-F/TP	120	3	4.3	270		2700	82	25W	15,000	Yes	★	Damp	Frost, Blunt Tip					
Globes																				
	MED	1.8	62992	LED2G16M-W/ES/TP	120	3	3.2	75		3000	80	10W	15,000	-	★	Dry	White			
			62993	LED2G16M-C/ES/TP	120	3	3.2	75		3000	80	10W	15,000	-	★	Dry	Clear			
		2	76451	LED2G16M/W/TP	120	3	3.2	60		2900	82	-	12,000	-	-	-	Dry	White		
			62990	LED2G16C-W/ES/TP	120	3	3	75		3000	80	10W	15,000	-	★	Dry	White			
		2.2	62991	LED2G16C-C/ES/TP	120	3	3	75		3000	80	10W	15,000	-	★	Dry	Clear			
			76449	LED2G16C/W/TP	120	3	3	60		2900	82	-	12,000	-	-	-	Dry	White		
		4.5	76450	LED2G16C/C/TP	120	3	3	60		2900	82	-	12,000	-	-	-	Dry	Clear		
			68169	LED4DG16C-W/TP	120	3	3.0	270		2700	82	25W	15,000	Yes	★	Damp	White			
		68170	LED4DG16C-C/TP	120	3	3.0	270		2700	82	25W	15,000	Yes	★	Damp	Clear				
			G25	2.3	63013	LED2G25M-W/ES/TP	120	3	4.3	95		3000	80	15W	15,000	-	★	Dry	White	
63014	LED2G25M-C/ES/TP				120	3	4.3	95		3000	80	15W	15,000	-	★	Dry	Clear			
2.8	76464			LED2G25M/W/TP	120	3	4.3	80		2900	82	-	12,000	-	-	-	Dry	White		
	78824			LED2G25M/W/TP	120	6	4.3	80		2900	82	-	12,000	-	-	-	Dry	White		
4.5	76465			LED2G25M/C/TP	120	3	4.3	80		2900	82	-	12,000	-	-	-	Dry	Clear		
	78825			LED2G25M/CLR	120	6	4.3	80		2900	82	-	12,000	-	-	-	Dry	Clear		
4.5	68171			LED4DG25M-W/TP	120	3	4.3	280		2700	82	25W	15,000	Yes	★	Damp	White			
	68172			LED4DG25M-C/TP	120	3	4.3	280		2700	82	25W	15,000	Yes	★	Damp	Clear			
Night Lights																				
	CAND			0.5	76422	LED1C7/W/CD2	120	6	2			2800	-	-	12,000	-	-	-	Dry	Frost
		78953	LED1C7/C/CD2		120	6	2			2700	-	-	12,000	-	-	-	Dry	Clear		

Decorative Lamps (Indoor/Outdoor)

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Equivalent	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
Candles																		
	MED	2.4	65535	LED2CAM-IO-F/TP	120	3	3.8	100		3000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
			65541	LED2CAM-IO-830/F	120	48/6**	3.8	100		3000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
			65539	LED2CAM-IO-840/F	120	48/6**	3.8	100		4000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
		CAND	65536	LED2CAC-IO-F/TP	120	3	3.8	100		3000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
			65542	LED2CAC-IO-830/F	120	48/6**	3.8	100		3000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
			65540	LED2CAC-IO-840/F	120	48/6**	3.8	100		4000	80	15W	15,000	-	★	Wet	Clear, Fluted, Blunt tip	
S14 Shape																		
	MED	2.4	65537	LED2S14-IO-F/TP	120	3	3.4	100		3000	80	15W	15,000	-	-	-	Wet	Frosted
			65538	LED2S14-IO-C/TP	120	3	3.4	100		3000	80	15W	15,000	-	-	-	Wet	Clear
			65545	LED2S14-IO/830/F	120	48/6**	3.4	100		3000	80	15W	15,000	-	-	-	Wet	Frosted
			65546	LED2S14-IO/830/C	120	48/6**	3.4	100		3000	80	15W	15,000	-	-	-	Wet	Clear
			65543	LED2S14-IO/840/F	120	48/6**	3.4	100		4000	80	15W	15,000	-	-	-	Wet	Frosted
			65544	LED2S14-IO/840/C	120	48/6**	3.4	100		4000	80	15W	15,000	-	-	-	Wet	Clear

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: Certified as meeting ENERGY STAR® guidelines.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

^ Incandescent or Halogen wattage equivalencies based on ENERGY STAR® guidelines using lumens or CBCP according to lamp type

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 66390, 65385, 64128, 65386, 64130 and 64018

Get more information at
GELighting.com/ThinkLED