



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED43T896G850D 43W Led T8 96" 50K Line Volt Glass Single Pin

*Keystone Technologies*

|                  |  |
|------------------|--|
| Catalog Number   | LED43T896G850D   |
| Manufacturer     | Keystone Technologies  |
| Description      | Linear Fluorescent Led Lamp, Linear, Double Ended, Instant Start Type; 93.31 Inch; UI (Canada and Us), UI, NSF/Ansi, DLC Approval; 120 to 277 Volt Ac Voltage Rating; 0.36 Amp At 120 Volt Ac, 0.16 Amp At 277 Volt Ac Current Rating; 43 Watt Wattage |
| Weight per unit  | 1.4 (lbs/each)   |
| Product Category | Shape & Circular Lamps   |

### Features

|                   |  |
|-------------------|--|
| Beam Spread Angle | 325 Degree                                       |
| Current Rating    | 0.36 Amp at 120 Volt AC, 0.16 Amp at 277 Volt AC |
| Glass Finish      | FROSTED  |
| Intensity         | 5550 Lumen                                       |
| Item              | LED Tube   |
| Voltage Rating    | 120 to 277 Volt AC                               |
| Wattage           | 43 Watt  |

### Material, Color, and Finish

|                             |           |
|-----------------------------|-----------|
| Base Type                   | FA8 1-Pin |
| Color Rendering Index       | 80 A      |
| Color Temperature in Kelvin | 5000      |

### Dimensions and Weight

|        |            |
|--------|------------|
| Length | 93.31 Inch |
|--------|------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Additional Information | RoHS Compliant; Overall Dimension 1.08 Inch Width x 1.31 Inch Height; Efficacy 129 Lumen per Watt; Temperature -4 to 131 Deg F  |
| Commodity Description  | Led Linear Fluorescent Straight, U-Shape & Circular Lamps   |
| Description            | 43W LED T8 96" 50K LINE VOLT GLASS SINGLE PIN   |
| extra long description | LINEAR, DOUBLE ENDED, INSTANT START TYPE; 93.31 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; 120 TO 277 VOLT AC VOLTAGE RATING; 0.36 AMP AT 120 VOLT AC, 0.16 AMP AT 277 VOLT AC CURRENT RATING; 43 WATT WATTAGE; LED TUBE; FA8 1-PIN BASE TYPE; 50000 LIFE IN HOUR; T8 SHAPE DESIGNATION; 5550 LUMEN INTENSITY; 5000; 80 COLOR RENDERING INDEX; FROSTED GLASS FINISH; 325 DEGREE BEAM SPREAD ANGLE; DIRECTDRIVE BRAND; ROHS COMPLIANT; OVERALL DIMENSION 1.08 INCH WIDTH X 1.31 INCH HEIGHT; EFFICACY 129 LUMEN PER W |
| Long Description       | LINEAR FLUORESCENT LED LAMP, LINEAR, DOUBLE ENDED, INSTANT START TYPE; 93.31 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; 120 TO 277 VOLT AC VOLTAGE RATING; 0.36 AMP AT 120 VOLT AC, 0.16 AMP AT 277 VOLT AC CURRENT RATING; 43 WATT WATTAGE  |
| Product Type           | Linear Fluorescent Led Lamp   |

## Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | Keystone Technologies |
| GTIN                      | 00890949019252        |
| Manufacturers Part Number | KT-LED43T8-96G-850-D  |
| Model                     | 800                   |
| UPC                       | 890949019252          |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type                 | Linear, Double Ended, Instant Start                              |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 10  |
| Weight Per each | 1.4 |

## Uses, Certifications, and Standards

|          |                                       |
|----------|---------------------------------------|
| Approval | UL (Canada and US), UL, NSF/ANSI, DLC |
|----------|---------------------------------------|