

# Specifications



## Eaton L1520RW

Eaton Arrow Hart watertight locking receptacle, #18-10 AWG, 20A, Industrial, 250V, Back wiring, Yellow, Steel, Single, Watertight, L15-20, Three-pole, Four-wire, Thermoplastic, 0.36 to 0.84 in, IP67

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart watertight locking receptacle
<b>CATALOG NUMBER</b>	L1520RW
<b>UPC</b>	040893687766
<b>PRODUCT LENGTH/DEPTH</b>	6.75 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	4.25 in
<b>PRODUCT WEIGHT</b>	1.025 lb
<b>COMPLIANCES</b>	Federal Specifications Classification W-C375
<b>CERTIFICATIONS</b>	cULus Listed NOM UL Listed CSA certified
<b>PRODUCT TYPE</b>	Watertight



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	20A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L15-20
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4 Grounding
RECEPTACLE TYPE	Locking
TORQUE RATING	For #10-14 AWG: 14-16 lbf-inch. For #8 AWG: 20 lbf-inch
VOLTAGE RATING	3Ø 250 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#14-8 AWG Copper, or Copper-Clad Aluminum
WIRING METHOD	Back

## Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.36-0.84 in
DESIGN TYPE	Single receptacle
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Glass filled nylon
MATERIAL	Thermoplastic
SPECIAL FEATURES	Watertight
TYPE	Locking receptacle

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

## Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 3
	NEMA 12
	NEMA 3R
	NEMA 4
	NEMA 4X
	IP66

## Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated bronze

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - L1520RW</a>
	<a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton L1520RW

Eaton Arrow Hart watertight locking receptacle, #18-10 AWG, 20A, Industrial, 250V, Back wiring, Yellow, Steel, Single, Watertight, L15-20, Three-pole, Four-wire, Thermoplastic, 0.36 to 0.84 in, IP67

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart watertight locking receptacle
<b>CATALOG NUMBER</b>	L1520RW
<b>UPC</b>	040893687766
<b>PRODUCT LENGTH/DEPTH</b>	6.75 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	4.25 in
<b>PRODUCT WEIGHT</b>	1.025 lb
<b>COMPLIANCES</b>	Federal Specifications Classification W-C375
<b>CERTIFICATIONS</b>	cULus Listed NOM UL Listed CSA certified
<b>PRODUCT TYPE</b>	Watertight



Powering Business Worldwide

## Electrical Ratings

AMPERAGE RATING	20A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L15-20
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4 Grounding
RECEPTACLE TYPE	Locking
TORQUE RATING	For #10-14 AWG: 14-16 lbf-inch. For #8 AWG: 20 lbf-inch
VOLTAGE RATING	3Ø 250 V

## Installation Specifications

ALLOWABLE WIRE SIZE	#14-8 AWG Copper, or Copper-Clad Aluminum
WIRING METHOD	Back

## Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.36-0.84 in
DESIGN TYPE	Single receptacle
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Glass filled nylon
MATERIAL	Thermoplastic
SPECIAL FEATURES	Watertight
TYPE	Locking receptacle

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

## Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 3
	NEMA 12
	NEMA 3R
	NEMA 4
	NEMA 4X
	IP66

## Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated bronze

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - L1520RW</a>
	<a href="#">Arrow Hart watertight locking plugs, connectors and receptacles spec sheet</a>



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

