

LED replacement lamps

Decorative Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information	
Candles																		
	CA11	MED	3.5	68168	LED3DCAM-C/TP	120	3	4.2	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip	
			4	68167	LED4DCAM-F/TP	120	3	4.2	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip	
				23707	LED4DCAM-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
			21250	LED4DCAM-C3/827	120	6	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip		
			75554	LED4DCAMCF/824	120	6	4.2	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip		
	4.5		23706	LED4.5DCAM-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
			89950	LED4.5DCAM-F/TP	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
		7	21251	LED7DCAM-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip		
		CAND	3.5		68166	LED3DCAC-C/TP	120	3	4.3	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip
					68165	LED4DCAC-F/TP	120	3	4.3	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip
	23691			LED4DCAC-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
			21231	LED4DCAC-C3/827	120	6	4.3	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip		
			75553	LED4DCACCF/824	120	6	4.3	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip		
	4.5	22239	LED4.5DCAC-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip			
	7	21233	LED7DCAC-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip			
	Globes																	
	G16.5	CAND	4.5	68169	LED4DG16C-W/TP	120	3	3.0	270	2700	82	25W	15,000	Yes	★	Damp	White	
				68170	LED4DG16C-C/TP	120	3	3.0	270	2700	82	25W	15,000	Yes		Damp	Clear	
	G25	MED	4.5	68171	LED4DG25M-W/TP	120	3	4.3	280	2700	82	25W	15,000	Yes	★	Damp	White	
				68172	LED4DG25M-C/TP	120	3	4.3	280	2700	82	25W	15,000	Yes		Damp	Clear	
					21253	LED5DG25-W3/827	120	6	4.3	350	2700	80	40W	15,000	Yes	★	Damp	White
				7	21255	LED7DG25-W3/827	120	6	4.3	500	2700	80	60W	15,000	Yes	★	Damp	White

Filament Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Candles																	
	ST19	MED	5	33025	LED5DST19-V-OT2P	120	8	5	440	2500		40W	15,000	Yes		Damp	4, 2-packs, Vintage Filament

Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.

UL 1993 Environmental Requirements for LED LAMPS

Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.

2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at

GELighting.com/ThinkLED

LED replacement lamps

Decorative Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Candles																	
	CA11	MED	3.5	68168	LED3DCAM-C/TP	120	3	4.2	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip
			4	68167	LED4DCAM-F/TP	120	3	4.2	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip
			23707	LED4DCAM-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
			21250	LED4DCAM-C3/827	120	6	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
	4.5	75554	LED4DCAMCF/824	120	6	4.2	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip		
		23706	LED4.5DCAM-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
		89950	LED4.5DCAM-F/TP	120	3	4.2	300	2700	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
		7	21251	LED7DCAM-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip	
	CAND	3.5	68166	LED3DCAC-C/TP	120	3	4.3	170	2700	80	25W	15,000	Yes	★	Damp	Clear, Bent tip	
			68165	LED4DCAC-F/TP	120	3	4.3	270	2700	82	25W	15,000	Yes	★	Damp	Frost, Bent tip	
			23691	LED4DCAC-C/5K/TP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip	
			21231	LED4DCAC-C3/827	120	6	4.3	300	2700	80	40W	15,000	Yes	★	Damp	Clear, Bent tip	
	4.5	75553	LED4DCACCF/824	120	6	4.3	250	2400	80	25W	15,000	Yes		Damp	Clear, Bent tip		
		22239	LED4.5DCAC-F5KTP	120	3	4.2	350	5000	80	40W	15,000	Yes	★	Damp	Frost, Bent tip		
		7	21233	LED7DCAC-C3/827	120	6	4.8	500	2700	80	60W	15,000	Yes	★	Damp	Clear, Bent tip	
		Globes															
	G16.5	CAND	4.5	68169	LED4DG16C-W/TP	120	3	3.0	270	2700	82	25W	15,000	Yes	★	Damp	White
			68170	LED4DG16C-C/TP	120	3	3.0	270	2700	82	25W	15,000	Yes		Damp	Clear	
	G25	MED	4.5	68171	LED4DG25M-W/TP	120	3	4.3	280	2700	82	25W	15,000	Yes	★	Damp	White
				68172	LED4DG25M-C/TP	120	3	4.3	280	2700	82	25W	15,000	Yes		Damp	Clear
			7	21253	LED5DG25-W3/827	120	6	4.3	350	2700	80	40W	15,000	Yes	★	Damp	White
				21255	LED7DG25-W3/827	120	6	4.3	500	2700	80	60W	15,000	Yes	★	Damp	White

Filament Lamps

Bulb Shape	Base Type	Watts	Order Code	Description	Volts	Case Qty**	MOL (In)	Lumens Initial	CBCP	Initial Color Temp	CRI	Wattage Replacement	*Rated Life L70 (Hrs)	Dimmable	ENERGY STAR® Status	#Location Rating	Additional Information
Candles																	
	ST19	MED	5	33025	LED5DST19-V-OT2P	120	8	5	440	2500		40W	15,000	Yes		Damp	4, 2-packs, Vintage Filament

Updated / New Product

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)
** Minimum order quantity = 6
★ ENERGY STAR® status: ENERGY STAR® certified. Lamps without a ★ are not ENERGY STAR® certified.
UL 1993 Environmental Requirements for LED LAMPS
Location, damp - Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.
Location, dry - Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.
Location, wet - Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.
Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.
2) LED A19 Locking device works on PC: 85791, 85792, 89898, 62182, 89899 and 89900

Get more information at
GELighting.com/ThinkLED