#### **Instructions/Installation Manual** LED-8088M





#### **Notes:**

SKU (USA)

LED-8088M30

LED-8088M40

LED-8088M57

- 1. Before beginning installation of LED for HID lamp, please read the complete instructions list below. Keep this document for future reference
- 2. To avoid possible electric shock, power supply must be turned off at fuse box or circuit breaker before installing or servicing.
- 3. Dropping, over torqueing screw base or impacting lamp during installation may cause damage and may void warranty.
- 4. Risk of Fire: High voltage wiring connecting the fixture must have a temperature rated minimum of 194°F.
- 5. Before installation of any LED for HID model into existing HID fixture, check your local electrical code. This code sets wiring standards for your area and should carefully studied before starting installation
- 6. Protect the lamp from dust and dirt, clean with soft damp cloth only, do not use chemical cleaners.
- 7. Ensure that outdoor fixture is sealed per manufacturers recommendations to reduce dust and insects from gaining entry.
- 8. When installing LED-8000 series retrofit lamps within HID fixtures, ballast must be bypassed when present.
- 9. 8000 series retrofits are UL damp rated, sealing the fixtures after installation will deliver best results.
- 10. Installing surge/lightning protectors is highly recommended and helps to eliminate premature driver failure caused by surges and other power fluctuations.
- 11. The recessed luminaire can not use with through-branch wiring.

### <u>Contents:</u>

T LC2	LED Retrofit lamp
1 PCS	Re-lamping label
1 PCS	Instruction/
	Installation Manual

<u>REQUIREMENTS</u>			
Input Voltage:	USA	Canada	
Imput voitage.	120-277VAC	120-347VAC	
Frequency:	50/60Hz		
Base:	E39 Mogul		
Ammuovad	Recessed		
Approved Housings:	Open (indoor)		
riousings.	<b>Enclosed (Outdoors)</b>		
Min. Housing Size: (Inches)			
Height:	11.9"		
Diameter:	5.4"		



#### **IMPORTANT SAFETY INSTRUCTIONS FOR LED RETROFIT CONVERSION:**

FOR USE ONLY WITH HID LUMINAIRES IN ACCORDANCE WITH THE INSTRUCTIONS PROVIDED WITH THIS RETROFIT KIT.



MARNING - RISK OF FIRE OR ELECTRICAL SHOCK, LED retrofit kit installation requires knowledge of luminaires electrical systems. If not qualified, do not attempt installation. Contact a qualified electrician.



**MARNING - RISK OF FIRE OR ELECTRICAL SHOCK.** Install this kit only in the luminaires that have the construction features and dimensions shown in the photographs and/or drawings and where the input rating of the retrofit kit does not exceed the input rating of the luminaire.



MARNING - Do not make or alter any open holes in an enclosure of wiring or electrical components during kit installation.



**MARNING -** To prevent wiring damage or abrasion, do not expose wiring to sharp edges of housing or other sharp surface.



**WARNING** - Not for use with HID ballast, 120-277VAC(USA)/120-347VAC(Canada) direct line voltage only.

THIS DEVICE IS NOT INTENDED FOR USE WITH EMERGENCY EXITS.



188 S. Northwest Highway 

Cary, IL 60013 cient Design (847) 380-3540 • FAX: (847) 380-3542 www.led-llc.com

## LED-8088M

# **Instructions/Installation Manual**



 SKU (USA)
 SKU (Canada)
 Description

 LED-8088M30
 LED-8088M30C
 50W 3000K

 LED-8088M40
 LED-8088M40C
 50W 4000K

 LED-8088M57
 LED-8088M57C
 50W 5700K

#### **Installation:**

**Step 1:** Disconnect Electrical Power to fixture.

Step 2: Remove or wire past the ballast where applicable.

Step 3: Connect the two common wires from the power source directly to the

corresponding leads to the socket. NOTE: The screw of the

lamp holder shall be connected to the NEUTRAL wire (white or gray)

Step 4: Attach the retrofit lamp to the female socket of the existing luminaire.

To avoid damaging lamp do not over-torque or overtightenlamp.

The E39 mogul female lamp holder shouldhave suitable mounting

strength to securely hold lamp in place.


Step 5: Align lamp in housing by holding base clamp (see diagram) while de-


rotating lamp body until desired aim point is achieved.


Step 6: Apply the silver adhesive label to the inside of the luminaire where it

will be visible during re-lamping.

**Step 7:** Turn on electrical power to the fixture.







**Before Rewiring** 

Disconnect and/or Remove Ballast

**Socket Wiring Diagram** 

