



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1620P 20A 4W 480V 3PH TL Plug

Pass & Seymour/Legrand

Catalog Number	L1620P
Manufacturer	Pass & Seymour/Legrand
Description	Locking Device Turnlock Plug, 20 A, 480 V, 2 Poles, 3 Wires, Black/White, Nylon Material, -40 °C Operating Temperature, +75 °C Operating Temperature, 2.20 In;0.225 to 1.150 In (Cord) Diameter, Plug Mount, 3.75 In Length, #18 to #8 Awg Wire Size, Impact and Corrosion Resistant, 0.34 LB
Weight per unit	0.3440 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20 A
Poles	2 in

Dimensions and Weight

Size	3.8 in
------	--------

Descriptions

Description	20A 4W 480V 3PH TL PLUG
-------------	-------------------------

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007162042
sub brand	Pass & Seymour
UPC	785007162042

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlock Plug

Packaging

Carton	1
Weight Per each	0.344

Uses, Certifications, and Standards

Mounting	Plug
standard	UL 498

20 AMP NEMA PLUG L1620 - BLACK BACK, WHITE FRONT BODY

L1620P | [Pass & Seymour](#)



FEATURES & BENEFITS

Turnlok Plug 4wire 20amp 3phase 480v



PRODUCT
ENVIRONMENTAL PROFILE

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

SPECIFICATIONS

GENERAL INFO

Color: Black, White

Type: Plug

Number Of Wires: 4

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 2.20"

Length (US): 3.75"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L1620

Volts: 480V

Volts (AC): 480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

