

TECHNICAL DATA SHEET

Cable Tie, standard, 18 lbs. series

Natural and UV resistant black

Catamount*



Ratings:

• Min. Bundle Dia: 0.06" (1.6 mm)

• Max. Bundle Dia: 0.75" (19mm)

• Tensile Strength: 18lb (80N)

• Min. Operating Temperature: -40°F (-40°C)

• Max. Operating Temperature: 185°F (85°C)

• Min. Installation Temperature: -32°F (0°C)

Installation:

 Install with approved ABB cable tie tool such as ERG50, QC-100, L-200, L-400-C

Materials / Finishes:

- Natural Polyamide (Nylon 6.6)
- UV-resistant black (Nylon 6.6)

Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle.

Certifications / Standards:








3-Part Specification: End User Tools

Conforms to:

- RoHS (Restriction of Hazardous Substance
 - European Directive 2011/65 and Commission
 Delegated Directive 2015/863



Product selection - in. (mm)					
Part no: GID no:	A ± 0.125 (3.0)	±0.01 (0.25)	±0.03 (0.76)	±0.03 (0.76)	±0.01 (0.25)
L-4-18-9-M 7TAG054060R0022	4.1 (105)	0.1 (2.4)	0.17 (4.3)	0.19 (4.8)	0.04 (1.1)
L-4-18-9-C 7TAG054020R0003					
L-4-18-0-C 7TAG054030R0003					
L-4-18-0-M 7TAG054070R0008					

Note: Product must be installed in accordance with applicable national and local electrical codes.

- -0 in part number = UV resistant black
- -9 in part number = Natural

tnb.ca.abb.com (Canada) abb.com