

Specifications

Eaton L530CW

Eaton Arrow Hart watertight locking connector, #18-10 AWG, 30A, Industrial, 125V, Back wiring, Yellow, Steel, Watertight, L5-30, Two-pole, Three-wire, Santoprene thermoplastic elastomeric, 0.43 to 1.15 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking connector
CATALOG NUMBER	L530CW
UPC	040893641867
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	1.025 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	NOM UL Listed CSA certified cULus Listed
PRODUCT TYPE	Watertight



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L5-30
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	Grounding 3
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	125 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
DESIGN TYPE	Watertight locking connector
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene thermoplastic elastomeric
SPECIAL FEATURES	Watertight
TYPE	Locking connector

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 6P
	NEMA 4
	IP67
	NEMA 4X
	NEMA 6

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L530CW
	Arrow Hart watertight locking plugs, connectors and receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton L530CW

Eaton Arrow Hart watertight locking connector, #18-10 AWG, 30A, Industrial, 125V, Back wiring, Yellow, Steel, Watertight, L5-30, Two-pole, Three-wire, Santoprene thermoplastic elastomeric, 0.43 to 1.15 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking connector
CATALOG NUMBER	L530CW
UPC	040893641867
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	1.025 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	NOM UL Listed CSA certified cULus Listed
PRODUCT TYPE	Watertight



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	30A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L5-30
NUMBER OF POLES	Two-pole
NUMBER OF WIRES	Grounding 3
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	125 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
DESIGN TYPE	Watertight locking connector
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene thermoplastic elastomeric
SPECIAL FEATURES	Watertight
TYPE	Locking connector

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 6P
	NEMA 4
	IP67
	NEMA 4X
	NEMA 6

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L530CW
	Arrow Hart watertight locking plugs, connectors and receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

