



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LRF20CR2BPWH Occupancy Sensor White

Lutron

Catalog Number	LRF20CR2BPWH
Manufacturer	Lutron
Description	Ceiling Occupancy Sensor, 14 A, 3 V DC, 324 to 676 SQ.FT A;30.2 to 62.4 M^2 A;360 ° Coverage, CR123 Lithium Battery, 10 Yr Battery Life, 1 Min to 30 Min Time Delay, 3.57 In Width, 1.13 In Height, Light Almond, 5 Yr Warranty, +32 °F Operating Temperature, +104 °F Operating Temperature
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

media	Yes
sensing range	324 ft2 (30.2 m2) to 676 ft2 (62.4 m2), 360 degree field of view
supply voltage	3

Descriptions

Description	LUTRON OCCUPANCY SENSOR 1 WAY FM 434 R2
extra long description	LUT LRF2-OCR2B-P-WH Radio Powr Savr
Special Features	Battery-powered passive infrared (PIR) sensor that automatically controls lights via RF communication to compatible dimming and switching devices. This sensor detects the heat from people moving within an area to determine when the space is occupied. The sensor then wirelessly transmits the appropriate commands to the associated dimming and switching devices to turn the lights on or off automatically. Combines both convenience and exceptional energy savings potential along with ease of installation. Has 3

Manufacturer Information

GTIN	00027557831970
UPC	027557831970

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless occupancy/vacancy sensor

Packaging

Carton	1
Package	6
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	CEILING
standard	cUL, FCC, IC, COFETEL, ANATEL, SUTEL