



## PAR LAMPS : PAR 30 & PAR30SN

### DESCRIPTION

LED PAR Replacement Lamps directly replace incandescent PAR lamps at a fraction of the energy cost.

### FEATURES

- Compatible with a wide array of dimmers
- +25,000 hour rated life for ENERGY STAR® Approved lamps\*
- 50,000 hour design life\*\*
- Up to 80% electricity savings vs. halogen
- 25° and 40° beam angles available
- No mercury or UV/IR emissions
- Shatter-resistant for reduced risk of injury and breakage

### WARRANTY

- 5 year limited warranty; see eiko.com for warranty details

### APPLICATIONS

- Recessed / Track Lighting
- Property Management
- Accent / Display Lighting
- Retail / Residential
- Hospitality
- Houses of Worship
- Healthcare
- Task Lighting



\* Early initial qualification for ENERGY STAR allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass ENERGY STAR requirements, manufacturers may increase the lifetime of a product as dictated by ENERGY STAR guidelines. See [http://www.energystar.gov/index.cfm?fuseaction=products\\_for\\_partners.showLightbulbs](http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs) for further details.

\*\* Design life is based on engineering testing and probability analysis



<b>PERFORMANCE</b>	Power Consumption	11W
	Lumens	850
	Efficacy (LPW)	77
	CRI	80+
	Beam	25°, 40°
	CCT	2700K, 3000K, 4000K
	Life (L70)	25,000 hours*
<b>ELECTRICAL</b>	Power Factor	>0.7
	THD	<20%
	Input Voltage	120V
<b>CONSTRUCTION</b>	Operating Temperature	-40°F to 104°F (-40°C to 40°C)
	Base	E26
<b>LISTINGS</b>	Certification(s)	ENERGY STAR® Rated; cULus Classified
	Material Usage	RoHS Compliant; no mercury or lead
	Environment	Not for use in enclosed fixtures, with electronic timers, photocells, or motion/occupancy sensors

## PERFORMANCE SUMMARY

### PAR30:

Order Code	Item #	Lumens	Watts	CBCP	CCT	CRI	Beam	MOL	Life/Hours	Replaces Incan.	Wet Location Rated	ES
09993	LED11WPAR30/FL/827-DIM-G8	850	11W	1917	2700K	80+	40°	4.57"	25K	75W	💧	★
10070	LED11WPAR30/FL/830-DIM-G8	850	11W	1564	3000K	80+	40°	4.57"	25K	75W	💧	★
10071	LED11WPAR30/FL/840-DIM-G8	850	11W	1605	4000K	80+	40°	4.57"	25K	75W	💧	★
09994	LED11WPAR30/FL/850-DIM-G8	850	11W	1809	5000K	80+	40°	4.57"	25K	75W	💧	★
10072	LED11WPAR30/NFL/827-DIM-G8	850	11W	2326	2700K	80+	25°	4.57"	25K	75W	💧	★
10073	LED11WPAR30/NFL/830-DIM-G8	850	11W	2415	3000K	80+	25°	4.57"	25K	75W	💧	★
10074	LED11WPAR30/NFL/840-DIM-G8	850	11W	2548	4000K	80+	25°	4.57"	25K	75W	💧	★

### PAR30SN:

Order Code	Item #	Lumens	Watts	CBCP	CCT	CRI	Beam	MOL	Life/Hours	Replaces Incan.	Wet Location Rated	ES
10075	LED11WPAR30S/FL/827-DIM-G8	850	11W	1644	2700K	80+	40°	3.62"	25K	75W		★
10076	LED11WPAR30S/FL/830-DIM-G8	850	11W	1536	3000K	80+	40°	3.62"	25K	75W		★
10077	LED11WPAR30S/FL/840-DIM-G8	850	11W	1586	4000K	80+	40°	3.62"	25K	75W		★
10078	LED11WPAR30S/NFL/827-DIM-G8	850	11W	2460	2700K	80+	25°	3.62"	25K	75W		★
10079	LED11WPAR30S/NFL/830-DIM-G8	850	11W	2415	3000K	80+	25°	3.62"	25K	75W		★

NOTE: Use order code when ordering. 💧Wet Location Rated ★ENERGY STAR® Approved

## DIMENSIONS

