



GE
Lighting

65137 - GE LED PAR30

LED12DP30S827/20

☞ Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	4400 cd
Lumens per Watt (Efficacy)	62 lm
Nominal Initial Lumen per Watt	62
Rated Beam Spread	20 deg
Initial Lumens-nominal	740 lm
Color Rendering Index-CRI	83
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	65137
Description	LED12DP30S827/20
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS


Voltage <Nom>	120 V
Rated power (Watts)	12 W



GE
Lighting

65137 - GE LED PAR30

LED12DP30S827/20

 Energy-efficient LED lamps. Long life.

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	4400 cd
Lumens per Watt (Efficacy)	62 lm
Nominal Initial Lumen per Watt	62
Rated Beam Spread	20 deg
Initial Lumens-nominal	740 lm
Color Rendering Index-CRI	83
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	65137
Description	LED12DP30S827/20
Alternative Unit Of Measure	CASE

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Rated power (Watts)	12 W