

Integrated LED Tubes

T8 U6 Plastic Tubes



Project Name _____

Date _____ Type _____

Notes _____

Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall. LED tubes are ideal for those seeking high energy savings with minimal installation time. Each LED tube is outfitted with an internal Current driver. Current integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.

PERFORMANCE HIGHLIGHTS:

T8 U6 Plastic Tubes	
Light Output Range:	1800-1900 Lumens
CRI:	80+
CCT:	3000K, 3500K, 4000K & 5000K
Wattage:	13W
Life:	50,000 hours L70
Temperature Rating:	-20°C to 40°C
Rating:	Damp
Fixtures:	Open or Enclosed
Dimming:	Dimmable with compatible dimming ballasts
Ballast Compatability Guide:	gecurrent.com/LEDTUBES-ballastcompatibility
Certification:	DLC Listed

BENEFITS:

- Fast and Easy LED upgrade
- Low energy LFL replacement
- 2X longer life than LFL (50,000 vs. 24,000 hours)
- Better quality of light-instant on
- Shatter resistant
- Easy disposal, non-hazardous waste

LEARN MORE:

To learn more about saving money and energy, go to www.gecurrent.com.

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

LIMITED WARRANTY

5 Years

Integrated LED Tubes

T8 U6 Plastic Tubes

Spec Table

Project Name _____

Date _____ Type _____

Notes _____

Type	Base Type	Order Code	Description	Low Normal High			Case Qty**	MOL (In)	Lumens Initial	Initial Color Temp	CRI	*Rated Life			# Location Rating	Additional Information
				BF Watts	BF Watts	BF Watts						L70 (Hrs)	DLC®	UL		
Integrated U6 Plastic Tubes																
T8	G13	43120	LED13ET8/U6/830	11	13	16	12	22.5	1800	3000K	80+	50,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	43125	LED13ET8/U6/835	11	13	16	12	22.5	1850	3500K	80+	50,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	43129	LED13ET8/U6/840	11	13	16	12	22.5	1900	4000K	80+	50,000	Yes	Yes	Damp	Instant or PRS Ballast
	G13	43130	LED13ET8/U6/850	11	13	16	12	22.5	1900	5000K	80+	50,000	Yes	Yes	Damp	Instant or PRS Ballast

Information provided is subject to change without notice. Please verify all details with Current. All values are design or typical values when measured under laboratory conditions, and Current makes no warranty or guarantee, expressed or implied, that such performance will be obtained under end-use conditions.

* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original rating (L70)

** Minimum order quantity = 6

UL 1993 Environmental Requirements for LED LAMPS

Location, damp – Exterior or interior location that is normally or periodically subject to condensation of moisture in, on, or adjacent to, electrical equipment, and includes partially protected locations.

Location, dry – Location not normally subject to dampness, may include a location subject to temporary dampness, i.e., building under construction, provided ventilation is adequate to prevent an accumulation of moisture.

Location, wet – Location in which water or other liquid can drip, splash, or flow on or against electrical equipment.

Notes: 1) Product descriptions ending in "/TP" indicate a carded blister or clamshell package nested in a tray for shelf display. Cards also designed for hook display.