






GE
Lighting

85379 - LU400/H/ECO

GE Ecolux® Lucalox® High Pressure Sodium ED18

- Passes TCLP, which can lower disposal costs.



CAUTIONS & WARNINGS

Caution

- Risk of Burn
 - Allow lamp to cool before handling.
 - Do not turn on lamp until fully installed.
- Lamp may shatter and cause injury if broken
 - Dispose of lamp in a closed container.
 - Do not use excessive force when installing lamp.
 - Do not use lamp if outer glass is scratched or broken.
 - Wear safety glasses and gloves when handling lamp.

Warning

- Contains sodium – chemical burn risk
 - Avoid skin contact with broken pieces.
- Unexpected lamp rupture may cause injury, fire, or property damage
 - Do not exceed rated voltage.
 - Do not store flammable materials near/below lamp.
 - Do not turn on lamp until fully installed.

For additional information, visit www.gelighting.com

GENERAL CHARACTERISTICS

Lamp Type	High Intensity Discharge - High Pressure Sodium ED18
Bulb	ED18
Base	Mogul Screw (E39)
Bulb Finish	Clear
Rated Life (MIN)	24000.0 h
Rated Life	24000.0 hrs
Bulb Material	Hard glass
Lamp Enclosure Type (LET)	Open or enclosed fixtures
Base Temperature (MAX)	210.0 °C
Bulb Temperature (MAX)	400.0 °C
LEED-EB MR Credit	15 picograms Hg per mean lumen hour
Additional Info	TCLP compliant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	51000.0
Mean Lumens	45000.0
Nominal Initial Lumens per Watt	127
Color Temperature	2100.0 K
Color Rendering Index (CRI)	22.0
Effective Arc Length	3.44 in

ELECTRICAL CHARACTERISTICS

Wattage	400.0
Voltage (MIN)	198.0
Burn Position	Universal burning position
Open Circuit Voltage (RMS lag ballast) (MIN)	198.0 V
Warm Up Time to 90%	4.0 min
Hot Restart Time to 90%	1.0 min

DIMENSIONS

Maximum Overall Length (MOL)	9.7500 in(247.6 mm)
Nominal Length	9.000 in(228.6 mm)
Bulb Diameter (DIA)	2.250 in(57.2 mm)
Light Center Length (LCL)	5.750 in(146.0 mm)


PRODUCT INFORMATION

Product Code	85379
Description	LU400/H/ECO
ANSI Code	S51
Standard Package	Case
Standard Package GTIN	10043168853795
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168853798

- Do not use lamp if outer glass is scratched or broken.
- Do not use where directly exposed to water or outdoors without an enclosed fixture.
- Use only properly rated ballast.
- Risk of Fire
 - Keep combustible materials away from lamp.
 - Use in fixture rated for this product.
- Risk of Electric Shock
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution








GE
Lighting

85379 - LU400/H/ECO

GE Ecolux® Lucalox® High Pressure Sodium ED18

- Passes TCLP, which can lower disposal costs.



GENERAL CHARACTERISTICS

Lamp Type	High Intensity Discharge - High Pressure Sodium ED18
Bulb	ED18
Base	Mogul Screw (E39)
Bulb Finish	Clear
Rated Life (MIN)	24000.0 h
Rated Life	24000.0 hrs
Bulb Material	Hard glass
Lamp Enclosure Type (LET)	Open or enclosed fixtures
Base Temperature (MAX)	210.0 °C
Bulb Temperature (MAX)	400.0 °C
LEED-EB MR Credit	15 picograms Hg per mean lumen hour
Additional Info	TCLP compliant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	51000.0
Mean Lumens	45000.0
Nominal Initial Lumens per Watt	127
Color Temperature	2100.0 K
Color Rendering Index (CRI)	22.0
Effective Arc Length	3.44 in

ELECTRICAL CHARACTERISTICS

Wattage	400.0
Voltage (MIN)	198.0
Burn Position	Universal burning position
Open Circuit Voltage (RMS lag ballast) (MIN)	198.0 V
Warm Up Time to 90%	4.0 min
Hot Restart Time to 90%	1.0 min

DIMENSIONS

Maximum Overall Length (MOL)	9.7500 in(247.6 mm)
Nominal Length	9.000 in(228.6 mm)
Bulb Diameter (DIA)	2.250 in(57.2 mm)
Light Center Length (LCL)	5.750 in(146.0 mm)

PRODUCT INFORMATION

Product Code	85379
Description	LU400/H/ECO
ANSI Code	S51
Standard Package	Case
Standard Package GTIN	10043168853795
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168853798

CAUTIONS & WARNINGS

Caution

- Risk of Burn
 - Allow lamp to cool before handling.
 - Do not turn on lamp until fully installed.
- Lamp may shatter and cause injury if broken
 - Dispose of lamp in a closed container.
 - Do not use excessive force when installing lamp.
 - Do not use lamp if outer glass is scratched or broken.
 - Wear safety glasses and gloves when handling lamp.

Warning

- Contains sodium – chemical burn risk
 - Avoid skin contact with broken pieces.
- Unexpected lamp rupture may cause injury, fire, or property damage
 - Do not exceed rated voltage.
 - Do not store flammable materials near/below lamp.
 - Do not turn on lamp until fully installed.

For additional information, visit www.gelighting.com

- Do not use lamp if outer glass is scratched or broken.
- Do not use where directly exposed to water or outdoors without an enclosed fixture.
- Use only properly rated ballast.
- Risk of Fire
 - Keep combustible materials away from lamp.
 - Use in fixture rated for this product.
- Risk of Electric Shock
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution

