



ESSENTIAL SERIES

GENERAL PURPOSE LED BULBS

KT-LED16A21-O-8XX-3W

REPLACEMENT LAMP

DESCRIPTION

A21 Lamp | 2700–5000K | >80 CRI | Omni-Directional | 3-Way Switch



LAMP TYPE: A21
BASE TYPE: E26 (Medium)
WATTAGE: 5.5W / 8W / 16W
COLOR TEMPERATURE: 2700–5000K
COLOR RENDERING INDEX (CRI): >80
WARRANTY: 3 Years
RATED LIFE: L70 (15,000 Hours)



TYPICAL APPLICATIONS

- Table, desk, and floor lamps
- Wall sconces
- Surface-mount ceiling fixtures
- General lighting
- Pendant lights

PRODUCT FEATURES

- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, diffused lens for comfortable glare-free performance
- Durable plastic housing lowers the risk for breakage
- Long life minimizes replacement and maintenance costs
- Suitable for use in damp locations
- ANSI compliant construction ensures fitment for intended applications
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF >0.70
- UL Listed
- UL enclosed rated, suitable for use in totally enclosed luminaires
- Meets Energy Star requirements
- Energy Star enclosed fixture rated
- Complies with Part 15 of FCC


ELECTRICAL AND PERFORMANCE SPECIFICATIONS

Keystone Catalog Number	Description	Color Temp	Input Voltage	Rated Lamp Wattage	Legacy Equivalent Wattage	Base Type	Lumens	CRI	Beam Angle	Dimmable	Efficacy
KT-LED16A21-O-827-3W	A21 bulb; Omni-directional; 3-way switch	2700K	120V	5.5W	40W halogen	E26	450 lm	>80	230°	No	82 lm/W
				8W	60W halogen		800 lm				100 lm/W
				16W	100W halogen		1600 lm				100 lm/W
KT-LED16A21-O-830-3W	A21 bulb; Omni-directional; 3-way switch	3000K	120V	5.5W	40W halogen	E26	450 lm	>80	230°	No	82 lm/W
				8W	60W halogen		800 lm				100 lm/W
				16W	100W halogen		1600 lm				100 lm/W
KT-LED16A21-O-850-3W	A21 bulb; Omni-directional; 3-way switch	5000K	120V	5.5W	40W halogen	E26	450 lm	>80	230°	NO	82 lm/W
				8W	60W halogen		800 lm				100 lm/W
				16W	100W halogen		1600 lm				100 lm/W

KT-LED16A21-O-8XX-3W

REPLACEMENT LAMP

PHYSICAL CHARACTERISTICS



LAMP DIMENSIONS

A (Diameter)	3.76"
B (Length)	5.16"

BASE TYPE: E26 (Medium)

PACKAGING

Carton Quantity	60 pcs
Carton Dimensions	18.15" × 15.24" × 12.52"
Carton Weight	19.6 lbs

ORDERING INFORMATION

ORDER CODE	CARTON QUANTITY	ITEM STATUS	EASY CODE	UPC
KT-LED16A21-O-827-3W	60 pcs	Active	TXN-49	843654126647
KT-LED16A21-O-830-3W	60 pcs	Active	MCR-46	843654126654
KT-LED16A21-O-840-3W	60 pcs	Active	ZUD-46	843654128924
KT-LED16A21-O-850-3W	60 pcs	Active	PDU-00	843654126661

CATALOG NUMBER BREAKDOWN

KT-LED16A21-O-8XX-3W

1 2 3 4 5 6 7 8

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Shape
- 5 Omni-Directional
- 6 800 Series
- 7 Color Temperature
- 8 3-Way Switch