



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street  
88201-0000, NM Roswell  
Phone: 575-208-1571  
Fax: 575-208-1572



## LED17PLL22G835D 17W Led T8 PLL 2G11 35K *Keystone Technologies*

Catalog Number	LED17PLL22G835D
Manufacturer	Keystone Technologies
Description	Compact Fluorescent Led Lamp, Non-Dimmable, Compact, Instant Start, PLL Type; 22.31 Inch; UI (Canada and Us), UI, NSF/Ansi, DLC Approval; Dry and Damp Location Application; 120 to 277 Volt Voltage Rating; 17 Watt Wattage; Led Lamp; 2G11 Base Type
Weight per unit	0.5700 (lbs/each)
Product Category	Integrated Lamps

### Features

Beam Spread Angle	220 Degree
Glass Finish	FROSTED
Intensity	2100 Lumen
Item	LED Lamp
Voltage Rating	120 to 277 Volt
Wattage	17 Watt

### Material, Color, and Finish

Base Type	2G11
Color Rendering Index	80 A
Color Temperature in Kelvin	3500

### Dimensions and Weight

Length	22.31 Inch
--------	------------

### Descriptions

Additional Information	RoHS Compliant; Size 1.73 Inch Width; Efficacy 124 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F
Commodity Description	Led Compact Fluorescent Integrated & Non-Integrated Lamps
Description	17W LED T8 PLL 2G11 35K
Long Description	COMPACT FLUORESCENT LED LAMP, NON-DIMMABLE, COMPACT, INSTANT START, PLL TYPE; 22.31 INCH; UL (CANADA AND US), UL, NSF/ANSI, DLC APPROVAL; DRY AND DAMP LOCATION APPLICATION; 120 TO 277 VOLT VOLTAGE RATING; 17 WATT WATTAGE; LED LAMP; 2G11 BASE TYPE
Product Type	Compact Fluorescent Led Lamp

### Manufacturer Information

Brand	Keystone Technologies
Manufacturers Part Number	KT-LED17PLL-22G-835-D
Model	800



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

907 East 2nd Street  
88201-0000, NM Roswell  
Phone: 575-208-1571  
Fax: 575-208-1572

## Taxonomies, Classifications, and Categories

Category Description	LED PLUG-IN (REPLACEMENT FOR CFL BIAX LAMPS)
Type	Non-Dimmable, Compact, Instant Start, PLL

## Packaging

Carton	1
Weight Per each	0.57

## Uses, Certifications, and Standards

Application	Dry and Damp Location
Approval	UL (Canada and US), UL, NSF/ANSI, DLC