3691057c 1 04.27.20

Maestro LED+ Fan/Light Control

Quiet fan-speed control with dimmer for dimmable LED and CFL bulbs.

Features


- LED+ includes the most advanced technology for superior dimming of LED, CFL, halogen, and incandescent bulbs.
- Tap on to preset light level/fan speed; tap off.
- Tap twice for full on.
- Touch rocker to adjust light level/fan speed.
- Four fan speeds plus off.
- Indicator lights display light level and fan speed.
- Single-pole only.
- No canopy module required.
- Requires separate wires for fan and light.
- No neutral wire required.
- UL Listed to control:
 - Dimmable LEDs
 - Dimmable compact fluorescent lamps (CFLs) with integrated ballast
 - Halogen
 - Incandescent
- Low-end adjustment to accommodate a wide range of bulbs.
- FASS Front Accessible Service Switch for fixture bulb replacement.
- Prevents tripping of AFCI breakers.
- 100% factory tested.
- Fault Detection / Indication
 - Light pull chain off detection
 - Lamp failure detection
 - Short circuit detection/protection
- Formerly C•L.

Product Specific Features

- Capable of controlling up to 75 W dimmable LED/CFL or 250 W incandescent/halogen lighting loads.
- Capable of controlling up to 1.5 A paddle-type ceiling fan loads.

Model Number¹

MACL-LFQ-XX Single-pole MACL-LFQH-XX² Single-pole MACL-LFQH-XX-C³ Single-pole



Wallplate sold separately

Colors and Finishes

White

Gloss Finishes

WH

AL	Almond	LA	Light Almond
GR	Gray	BR	Brown
BL	Black		
Satin	Colors		
SW	Snow	MN	Midnight
TP	Taupe	BI	Biscuit
ES	Eggshell	PD	Palladium
HT	Hot	MR	Merlot
PL	Plum	SI	Sienna
TC	Terracotta	BG	Bluestone
GB	Green Briar	GS	Goldstone
MS	Mocha Stone	ST	Stone
DS	Desert Stone	LS	Limestone

IV

Ivory

For the latest color offerings please see our website: http://www.lutron.com/satincolors

XX in the model number represents color/finish code; see section "Colors and Finishes" above.

² For clamshell packaging, add an "H" after "Q".

³ Clamshell packaged product for Canada.

LUTRON SPECIFICATION SUBMITTAL

Page Job Name: Model Numbers: Job Number:

3691057c 2 04.27.20

Specifications

Regulatory Approvals

- UL Listed to U.S. and Canadian safety requirements
 - UL 1472/CSA C22.2 184.1 (dimmer)
 - UL 1917 (fan)
 - NOM
- Meets requirements of NEMA SSL7-2015

Power and Ratings

- 120 V∼ 60 Hz
- 1.5 A fan rating single fan only
- 75 W dimmable LED/CFL or 250 W incandescent/halogen light rating

Environment

- For indoor use only
- Operating temperatures 32 °F (0 °C) to 104 °F (40 °C)
- 0% to 95% relative humdity, non-condensing


Performance

- Power-failure memory
- Electrostatic discharge tested
- Precise color matching
- Mechanical air-gap switch to disconnect load power
- Dual power supply for light pull chain off detection

Application Requirements

- When using LEDs or CFLs, only bulbs marked or rated as DIMMABLE can be used.
- For a complete list of approved DIMMABLE LEDs please visit www.lutron.com/LEDfinder
- Requires separate wires for fan and light.
- Not for use with DC motor fans or fans with remote controls.
- Not for use with bathroom or kitchen exhaust-type fans.

Dimensions



Note: Requires a U.S. wallbox 2½ in (64 mm) deep minimum.

Warranty

1 Year Limited Warranty
 For additional Warranty information, please visit www.lutron.com/TechnicalDocumentLibrary/369-119 Wallbox Warranty.pdf


LUTRON SPECIFICATION SUBMITTAL

*LOTHON SPECIFICATION SUBMITTAL			
Job Name:	Model Numbers:		
Job Number:			

Page

3691057c 3 04.27.20

Operation




LUTRON SPECIFICATION SUBMITTAL

3691057c 4 04.27.20

Wiring Diagrams

Single-Pole Wiring



The Lutron logo, Lutron, Maestro, $C \bullet L$, LED+, Satin Colors, and FASS are trademarks or registered trademarks of Lutron Electronics Co., Inc. in the US and/or other countries. All other product names, logos, and brands are property of their respective owners.

LUTRON SPECIFICATION SUBMITTAL

Page

Job Name:	Model Numbers:
Job Number:	