



KT-LED43T8-96GC-840-D

T8 LED LAMP

DESCRIPTION

43W T8 LED | 4000K | >80 CRI | High Efficiency | 8 Foot

Compliant



LAMP TYPE: Linear	COLOR TEMPERATURE: 4000K
BULB TYPE: T8 LED	COLOR RENDERING INDEX (CRI): >80
BASE TYPE: Fa8 (Single-Pin)	WARRANTY: 5 Years
WATTAGE: 43W	

PRODUCT FEATURES

- Replacement for Conventional T8/T12 8 Foot Single-Pin Fluorescent Lamp
- Double Ended Line Voltage Wiring: Connect power to each end for simplified installation
- 50.000+ Hour Lifetime
- Approximately 50% More Energy Efficient then Standard F96T12 Lamps
- Environmentally Friendly: No Mercury Used
- Instant Startup
- Includes 2 C-clips to be installed with the lamps into the fixture ballast cover to prevent any potential un-desired lamp twisting or sagging
- Frosted Lens Elimates Pixelation
- UL Classified

- Operating Temperature: -20°C/-4°F to 55°C/131°F
- Integral Driver (Isolated), Eliminates the Need for External Driver or Ballast
- 120+ Lumens per Watt
- Improved Lamp Durability with Shatterproof Coated Glass, designed to pass drop tests of 6' on hard surface
- NSF Listed: NSF/ANSI Standard 2 -Food Equipment, Splash Zone (Not for Direct Food Zone without additional fixture considerations)

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	43W	>0.9	0.36 @ 120V 0.16 @ 277V

PHOTOMETRIC CHARACTERISTICS


Color Temperature	4000K		
Luminous Flux	5500 lm		
Color Rendering Index (CRI)	>80		
Efficacy	128 lm/W		
Beam Angle	325°		

RATED LIFE


L70 (Hours)

50,000

SPECTRAL DISTRIBUTION



POLAR CANDELA DISTRIBUTION



Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com




KT-LED43T8-96GC-840-D

WIRING DIAGRAMS


1. Identify ballast configuration as shown below and cut all wires connected to the ballast accordingly.

Typical Ballast Configurations:




- 2. Confirm that the lampholders in the fixture are single-pin Fa8 lampholders. These DirectDrive LED tubes require single-pin Fa8 lampholders.
- 3. Rewire the fixture using existing lampholders as shown below according to the original ballast wiring configuration.

Typical Ballast Configurations:



PHYSICAL CHARACTERISTICS

LAMP DIMENSIONS



A (Illuminated Length)	91.5"		
B (Body Length)	93.31"		
C (Cross Section: Width x Height)	1.08" x 1.31"		

NOMINAL LENGTH: 96" BASE TYPE: Fa8 (Single-Pin)

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED43T8-96GC-840-D-CP	Distributor Pack (Individual Cartons)	10	Quick Ship

CATALOG NUMBER BREAKDOWN

KT-	LED	43	78	-96	GC	-840	-D-CP
Keystone Technologies	LED Lamp	Wattage	Lamp Type	Nominal Length (Inches)	Glass Coated	800 Color Series Temp.	Direct Packaging Drive Style Series

Keystone Technologies • 1390 Welsh Road, North Wales, PA 19454 • Phone (800) 464-2680 • Fax (888) 966-0556 • www.keystonetech.com

٦

BLUE