# **MC**<sup>AP</sup> Type MC All Purpose



14 AWG through 8 AWG Copper THHN Insulated Conductors. Full-Sized Aluminum Equipment Grounding/Bonding Conductor. UL Listed. 600 Volt. Rated VW1. Lightweight Aluminum Interlocked Armor is Part of Equipment Bonding/Grounding Path.

### APPLICATIONS

Southwire MC<sup>AP</sup> Type MC Cable - All Purpose is suitable for use as follows:

- Wherever standard AC or MC Cable is permitted.
- Branch circuit wiring in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22 (C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2).
- Use UL Listed Type MCI-A connectors


## **STANDARDS & REFERENCES**

#### Southwire MC<sup>AP</sup> Type MC Cable meets or exceeds the following:

- UL 83
- UL 1569
- UL 1063
- UL Online Product Guide Info Metal-Clad Cable (PJAZ) ( www.ul.com )
- NFPA 70 (National Electrical Code), Article 330
- Federal Specification A-A59544 (formerly J-C-30B)
- FT4/IEEE 1202 (70,000 Btu/hr) Vertical Cable Tray Flame Test
- Listed for use in UL 1, 2, and 3 Hour Through-Penetration Firestop Systems
- REACH/RoHS-2 (Chemical Limit) Compliant

### CONSTRUCTION

Southwire MC<sup>AP</sup> Type MC Cable is constructed with solid soft-drawn copper Type THHN circuit conductors rated 90° C dry and a full-sized bare 8000 Series aluminum grounding/bonding conductor. This cable is available in sizes 14-8 AWG. The insulated conductors are cabled together and wrapped with a binder tape bearing the print legend. The bare aluminum grounding/bonding conductor is located outside the binding tape and has the same lay as the insulated conductors. Aluminum interlocking armor is snugly applied over the assembly. The aluminum armor and bare aluminum conductor are in intimate contact and together form the equipment ground path. To insure proper installation, refer to the installation instructions provided with every reel and coil.





The Power of Connections. ™

©2016 Southwire Company, LLC. All rights reserved. ®Registered Trademark of Southwire Company, LLC. One Southwire Drive, Carrollton, GA 30119, USA

CONDUCTOR SIZE AND COLORS	GROUNDING/BONDING CONDUCTOR	STOCK NUMBER		WEICHT	OVERALL				
		COIL (250')	REEL (1000')	WEIGHT (LBS/1000')	DIAMETER (INCHES)				
SOLID CONDUCTOR COLORS 120/208V									
14-2 SOLID (BLACK/WHITE)	12 SOLID ALUMINUM	55-52-72-01	55-52-72-02	63	.375				
14-3 SOLID (BLACK/WHITE/RED)	12 SOLID ALUMINUM	55-52-73-01	55-52-73-02	81	.406				
14-4 SOLID (BLACK/WHITE/RED/BLUE)	12 SOLID ALUMINUM	55-52-74-01	55-52-74-02	98	.435				
12-2 SOLID (BLACK/WHITE)	10 SOLID ALUMINUM	55-51-03-01	55-51-03-02	86	.43				
12-2 SOLID (RED/WHITE)	10 SOLID ALUMINUM	55-87-68-01	55-87-68-02	86	.43				
12-2 SOLID (BLUE/WHITE)	10 SOLID ALUMINUM	55-87-70-01	55-87-70-02	86	.43				
12-3 SOLID (BLACK/WHITE/RED)	10 SOLID ALUMINUM	55-51-04-01	55-51-04-02	111	.447				
12-4 SOLID (BLACK/WHITE/RED/BLUE)	10 SOLID ALUMINUM	55-51-05-01	55-51-05-02	137	.48				
10-2 SOLID (BLACK/WHITE)	8 SOLID ALUMINUM	55-52-75-01	55-52-75-02	124	.485				
10-3 SOLID (BLACK/WHITE/RED)	8 SOLID ALUMINUM	55-52-77-01	55-52-77-02	164	.52				
10-4 SOLID (BLACK/WHITE/RED/BLUE)	8 SOLID ALUMINUM	55-52-78-01	55-52-78-02	204	.565				
STRANDED CONDUCTOR COLORS 120/208V									
12-2 STRANDED (BLACK/WHITE)	10 SOLID ALUMINUM	55-63-77-01	55-63-77-02	90	.437				
12-2 STRANDED (RED/WHITE)	10 SOLID ALUMINUM	55-87-86-01	55-87-86-02	90	.437				
12-2 STRANDED (BLUE/WHITE)	10 SOLID ALUMINUM	55-87-88-01	55-87-88-02	90	.437				
12-3 STRANDED (BLACK/WHITE/RED)	10 SOLID ALUMINUM	55-64-57-01	55-64-57-02	118	.468				
12-4 STRANDED (BLACK/WHITE/RED/BLUE)	10 SOLID ALUMINUM	55-58-74-01	55-58-74-01	145	.506				
10-2 STRANDED (BLACK/WHITE)	8 SOLID ALUMINUM	55-73-87-01	55-73-87-02	130	.508				
10-3 STRANDED (BLACK/WHITE/RED)	8 SOLID ALUMINUM	55-73-90-01	55-73-90-02	173	.548				
SOLID CONDUCTOR COLORS 277/480V									
12-2 SOLID (YELLOW/GRAY)	10 SOLID ALUMINUM	55-55-39-01	55-55-39-02	86	.43				
12-2 SOLID (BROWN/GRAY)	10 SOLID ALUMINUM	55-57-26-01	55-57-26-02	86	.43				
12-2 SOLID (ORANGE/GRAY)	10 SOLID ALUMINUM	55-55-38-01	55-55-38-02	86	.43				
12-3 SOLID (BROWN/YELLOW/GRAY)	10 SOLID ALUMINUM	55-55-41-01	55-55-41-02	111	.447				
12-3 SOLID (BROWN/ORANGE/GRAY)	10 SOLID ALUMINUM	55-57-28-01	55-57-28-02	111	.447				





©2016 Southwire Company, LLC. All rights reserved. ©Registered Trademark of Southwire Company, LLC. One Southwire Drive, Carrollton, GA 30119, USA

#### MC-AP Type MC All Purpose

12-4 SOLID (BROWN/ORANGE/YELLOW/GRAY)	10 SOLID ALUMINUM	55-57-31-01	55-57-31-02	137	.48			
10-2 SOLID (BROWN/GRAY)	8 SOLID ALUMINUM	55-57-33-01	55-57-33-02	124	.485			
10-3 SOLID (BROWN/ORANGE/GRAY)	8 SOLID ALUMINUM	55-57-35-01	55-57-35-02	164	.52			
10-4 SOLID (BROWN/ORANGE/YELLOW/GRAY)	8 SOLID ALUMINUM	55-57-37-01	55-57-37-01	204	.565			
STRANDED CONDUCTOR COLORS 277/480V								
12-2 STRANDED (YELLOW/GRAY)	10 SOLID ALUMINUM	55-87-93-01	55-87-93-02	90	.437			
12-2 STRANDED (BROWN/GRAY)	10 SOLID ALUMINUM	55-87-43-01	55-87-43-02	90	.437			
12-2 STRANDED (ORANGE/GRAY)	10 SOLID ALUMINUM	55-87-90-01	55-87-90-02	90	.437			
12-3 STRANDED (BROWN/ORANGE/GRAY)	10 SOLID ALUMINUM	55-87-45-01	55-87-45-02	118	.468			
12-4 STRANDED (BROWN/ORANGE/YELLOW/GRAY)	10 SOLID ALUMINUM	55-87-47-01	55-87-47-02	145	.506			

For allowable ampacities, refer to NEC 310.15.

Dimensions are nominal and subject to normal manufacturing tolerances and should be used for reference purposes only.

### **FEATURES**

- An armor assembly that is an equipment grounding conductor per NEC 250.118(10)(b).
- Installation instructions included with every reel and coil.
- Simplified product application and installation over other armored products.
- Faster conductor make-up, wiring device installation and trim-out when grounding/bonding conductor is terminated per installation instructions.
- Reduces installation costs up to 50% over pipe and wire.
- UL Classified 1, 2, and 3 hour Through Penetration Firestop Systems: W-J-3037, W-L-3110, W-L-3113, W-L-3117, W-L-3120, W-L-3121, W-L-3160, C-AJ-3115, C-AJ-3140, C-AJ-3142, C-AJ-3145, C-AJ-3173, C-AJ-3202, C-AJ-4065, C-AJ-4066, F-C-3038.
- Cable reverse wound on reel for ease of pulling and installation. When pulling from coils, pull from inside to ensure ease of installation.
- Anti-short bushings are not required for use with MC cable per the NEC and UL



The Power of Connections. ™