



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106



## LED7T824G8CSJDX2 7W Led T8 24" 3K/35K/4K/5K/65K SGL/DBL End - Glass *Keystone Technologies*

Catalog Number	LED7T824G8CSJDX2
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, 1000 Lumen, Glass Construction, 2FT, Color Select 3000/3500/4000/5000/6500K, 120-277V Input, Direct Drive, Single and Double Ended Wiring
Weight per unit	0.0160 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
Lamp Type	T8
lumens	1000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	Not Applicable - No Bulb
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	7W LED T8 24" 3K/35K/4K/5K/65K SGL/DBL END - GLASS
extra long description	Key KT-LED7T8-24G-8CSJ-DX2 7W LED T
Long Description	7W LED T8 Tube, 1000 lumen, Glass Construction, 2ft, Color Select 3000/3500/4000/5000/6500k, 120-277v Input, Direct Drive, Single and Double Ended Wiring
Product Type	7W Led T8 Tube, 1000 Lumen, Glass Construction, 2FT, Color S



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive  
79936-0000, TX El Paso  
Phone: 915-995-8443  
Fax: 915-245-2106

## Manufacturer Information

Brand	Keystone
GTIN	00843654141428
Manufacturers Part Number	KT-LED7T8-24G-8CSJ-DX2
UPC	843654141428

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.016

## Uses, Certifications, and Standards

Energy Star	N
-------------	---