Catamount® cable fastening accessories


SPECIFICATIONS:


MATERIAL: NYLON

ADHESIVE: SYNTHETIC RUBBER

MOUNTING SCREW SIZE: #6







NOTES:

- I.APPLICATION TEMPERATURE: 65°F TO 120°F (18°C TO 49°C) STORAGE/SERVICE TEMPERATURE: 32°F TO 158°F (0°C TO 70°C)
- 2.MECHANICAL STRENGTH: II LB / 50 N
- 3.SURFACE PREPARATION: SURFACE SHOULD BE CLEANED WITH ALCOHOL-BASED (IPA) CLEANER BEFORE APPLICATION.
- 4.APPLY WITH PRESSURE AND HOLD FOR 5 SECONDS.
- 5.BONDING TIME: 15 MINUTES MAXIMUM ADHESION: I HOUR
- 6. EXPIRATION DATE INDICATED ON PACKAGING.

CAT. No.	COLOR	Α	В	С	D	E	F
MPNY-1000-9-*	NATURAL	. 990	. 990	. 214	. 200	. 200	.060
MPNY-1000-0-*	BLACK	[25.140]	[25.140]	[5.436]	[5.080]	[5.080]	[1.520]

* DENOTES PACK QTY. "C"= 100, "D"= 500

I. ALL DIMENSIONS ARE FOR REFERENCE ONLY.		Thomas Betts www.inb.com A Member of the ABB Group					
۷.	DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.	DESCRIPTION: 1" x 1" CABLE TIE					
	REVISIONS	MOUNTING BASE					
SEE ERN (2017554) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: 054P000575	IVICOINTING BASE						
	FOR APPROVAL SIGNATURES	ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:		
	054P000575 / (2016272)	1 OF 1	1	WSD-001486			