

# Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy Catalog # MRC840

Crimper, #8-4/0 AWG CU.



#### **Features**

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- · Steel jaws

# **Application**

Crimping

#### General

Application - For Use On Copper Terminals and Splices
Die Type Rotating Die Wheel

EU RoHS Indicator Yes
Sub Brand HYTOOL

Tool Type Mechanical Rotating Crimper

 Trade Name
 HYTOOL™

 UPC
 781810192504

 UPC 12 Digit
 7818101925044

## **Dimensions**

Dimensions 26.00 in x 8.00 in x 1.50 in

 Height
 1.50 in

 Length
 26.00 in

 Weight
 8.25 lb

 Width
 8.00 in

#### **Conductor Related**

Crimping Ranges Copper: #8 AWG- #4/0 AWG

# **Certifications and Compliance**

Standards - RoHS Compliance EX

Status

#### Logistics

Minimum Pack Quantity

Package Contents Tool only

## **Product Assets**

Catalogs - Full Line BURNDY Catalog Installation Manuals - BUR\_50097800\_MRC840 Sales Drawings - SE..211280-01

