



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N3L Split Bolt Copper 3 3 WR

Nsi Industries

Catalog Number	N3L
Manufacturer	Nsi Industries
Description	3 Wire Copper Split Bolt Connector 3 Awg Copper Split Bolt Connectors Are High-Strength Solderless Service Connectors Made Of High-Copper Alloy For Copper and Copperweld Wires. Type For Three Maximum Wire Sizes.
Weight per unit	0.1100 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	3 STR - 10 STR
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER
Housing Material	Copper

Dimensions and Weight

Size	L=1.417 - W=.708
------	------------------

Descriptions

Description	SPLIT BOLT COPPER 3 3 WR
extra long description	NSI N-3L Split Bolt Copper 3 3 Wr
Features	3 Wire Copper Split Bolt Connector 3 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for three maximum wire sizes.
Long Description	3 Wire Copper Split Bolt Connector 3 AWG Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for three maximum wire sizes.
Product Type	Split Bolt Copper 3 3 WR
Special Features	3 STR-10 STR - 40 Pack

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381020239
Manufacturers Part Number	N-3L
UPC	662381020239



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Copper Split Bolts

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B