



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5004 National Parks highway  
88220-0000, NM Carlsbad  
Phone: 575-988-7017  
Fax: 575-988-7018



## LPCC2 2A 600V TD Class CC Low Peak Fuse

*Bussmann Fuses*

Catalog Number	LPCC2
Manufacturer	Bussmann Fuses
Description	Low Peak Fuse, Time Delay Fuse Speed, Class CC Fuse, 12 S @ 200% Response Time, 2 A, 600 V Ac;300 V DC, Melamine Tube Material, Dual Element, 0.41 In Diameter, 1.5 IN38.1 MM Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Current Limiting

### Features

amperage rating	2
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
element	Dual
media	Yes

### Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

### Descriptions

Description	2A 600V TD CLASS CC LOW PEAK FUSE
extra long description	BUSS LP-CC-2 LOW PEAK CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712180269
UPC	051712180269

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5004 National Parks highway  
88220-0000, NM Carlsbad  
Phone: 575-988-7017  
Fax: 575-988-7018

## Packaging

Carton	10
Weight Per each	0.02

## Uses, Certifications, and Standards

standard	UL Listed ,CSA Certified,CE Marked,RoHS Compliant
----------	---