
Eaton LP-CC-25

Catalog Number: LP-CC-25

Eaton Bussmann series LP-CC fuse, Current-limiting time-delay fuse, Rejection style, 25 A, Dual, CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Melamine tube, 10



Product Name Eaton Bussmann series LP-CC fuse UPC 051712180283 Product Length/Depth

0.41 in

Product Width

0.41 in

Warranty Not Applicable Catalog Number LP-CC-25 EAN 5027590446983

Product Height 1.5 in

Product Weight 0.15 lb

Compliances CE Marked RoHS Compliant





Product specifications

Fuse indicator

Non-indicating

Special features

Rejection style

Interrupt rating 200 kAIC at 600 Vac 20 kAIC at 300 Vdc

Number of elements

Dual

Connection Ferrule end x ferrule end

Response time

12 sec at 200%

Quantity

10

Material

Melamine tube

Amperage Rating

25 A

Type Current-limiting time-delay fuse

Class

Class CC

Voltage rating 600 Vac, 300 Vdc

Application Specialized circuits and industrial control

Packaging type

Standard

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

LP-CC-25~LOW PEAK CC TIME DELAY

Bussmann series complete full line catalog no. 1007

Multimedia Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - LP-CC-25

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia