



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LRF20KLBPWH Corner Occupancy Sensor White

Lutron

Catalog Number	LRF20KLBPWH
Manufacturer	Lutron
Description	Radio Powr Savr Wireless Occupancy/Vacancy Sensor, Corner-Mount, 434 MHZ, White Finish
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

media	Yes
sensing range	1225 ft2 (113.8 m2) minor motion, 2500 ft2 (232.3 m2) major motion, 90 degree field of view.
supply voltage	3

Descriptions

Description	CORNER OCCUPANCY SENSOR WHITE
extra long description	LUT LRF2-OKLB-P-WH LUTRON CORNER OC
Long Description	Radio Powr Savr Wireless Occupancy/Vacancy Sensor, Corner-mount, 434 MHz, White finish
Product Type	Lutron Corner Occ Sensor
Special Features	Battery-powered, passive infrared (PIR) sensors that automatically control lights via RF communication to compatible dimming or switching devices. These sensors detect the heat from people moving within an area to determine when the space is occupied. The sensors then wirelessly transmit the appropriate commands to the associated dimming or switching devices to turn the lights on or off automatically. They combine both convenience and exceptional energy savings along with ease of installation. Has 2 setti

Manufacturer Information

Brand	Lutron
GTIN	00027557823586
Manufacturers Part Number	LRF2-OKLB-P-WH
UPC	027557823586

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless wall-mount occupancy/vacancy sensor

Packaging

Carton	1
Weight Per each	0.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	Corner
Operating Temperature	32 to 104
standard	cULus, FCC, IC, COFETEL, ANATEL, SUTEL