



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT114UL 1-1/4" Ua Sealtite Conduit, Bonded UI 50' *Southwire Company*

Catalog Number	LT114UL
Manufacturer	Southwire Company
Description	TITAN2 Type UI LFMC Is Manufactured With A Spiral Wound Strip Of Heavy Gauge Corrosion-Resistant Hot-Dipped Galvanized Steel. For 3/8" Through 1-1/4" Trade Sizes The Core Is Constructed With A Square Locked Steel Strip With An Integral Copperbonding Strip Enclosed Within The Steel Convolutions. For 1-1/2" Through 4" Trade Sizes The Core Is Constructed With A Fully Interlocked Steel Strip. A Rugged Flame Retardant Flexible PVC Jacket Is Extruded Over The Steel Core. The Grey Jacket Resists Oils Mild
Weight per unit	0.6600 (lbs/each)
Product Category	Conduit & Raceways

Descriptions

extra long description	SWC 55093305 LTM-UL 1-1/4" GYJT 50C
Long Description	Titan2 Type UL LFMC is manufactured with a spiral wound strip of heavy gauge corrosion-resistant hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes the core is constructed with a square locked steel strip with an integral copperbonding strip enclosed within the steel convolutions. For 1-1/2" through 4" trade sizes the core is constructed with a fully interlocked steel strip. A rugged flame retardant flexible PVC jacket is extruded over the steel core. The grey jacket resists oils mild
Product Type	LTM-UI 1-1/4" Gyjt 50CN
Short Description	1" TITAN METAL-FLEX CONDUIT TY

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886042386
Manufacturers Part Number	55093305
UPC	032886042386

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	50
Weight Per each	0.66