

**BALLAST BYPASS**  
**LED Type B T8**

**Limitless Options**  
 for the following applications:

LED compatible replacement for linear fixtures that operate independently of ballasts.

- Offices
- Restaurants
- Retail Stores
- Lobbies
- Schools
- Hospitals



RECOGNIZED COMPONENT



Intertek  
4005203

**5** YEAR WARRANTY

CONFORMS TO NSF STD. 2

## Features and Benefits

>40% energy savings
Long life: 50,000
Bypass Application: 120-277 line voltage
Instant on/off
Non-flickering
Double ended construction
Shunted or non-shunted lampholders
UL rated for enclosed fixtures
No energy losses due to fluorescent ballast
Can be wired single ended

## Specifications

Base Types: G13
Construction: Double ended
Wattage: 13.5w, 15w, 19w, 22w, 25w
Minimum starting temperature range: -22F / -30C
Safety: UL Classified and ETL Classified
Environment: Damp/dry locations
Enclosed: Suitable for enclosed luminaires
Rated life: L70 50,000+ hours
Beam Angle: 190°
Field Angle: 300°

## Listing

UL Classified
Recognized Component ETL

## Warranty

Five years against defects in manufacturing
---------------------------------------------

### Shatterproof PET Coated Glass



### All Glass



### Plastic




**5** YEAR WARRANTY




To view our DLC qualified products, please consult the DLC Qualified Products List at [www.designlights.org/qpl](http://www.designlights.org/qpl).

### Double Ended Wiring



### Single Ended Wiring





LED Ballast Bypass Double Ended T8 Tubes

Item#	Description	DLC	LED Wattage	Voltage	Fluorescent Equivalency	Lumens	LPW	Base	CCT	CRI	Master Pack	Availability
<b>ALL GLASS</b>												
<b>LED 13.5 WATT ALL GLASS T8 TUBE – 4 FOOT (BULK PACK) (DLC LOOK UP T80415CXXE)#</b>												
LT813B230K	LED 13.5W 4' T8 2E BYPASS 30K (BULK PACK)		13.5	120-277V	32W	1800	133.3	G13	3000K	80	25	2
LT813B235K	LED 13.5W 4' T8 2E BYPASS 35K (BULK PACK)	*	13.5	120-277V	32W	1800	133.3	G13	3500K	80	25	2
LT813B241K	LED 13.5W 4' T8 2E BYPASS 41K (BULK PACK)	*	13.5	120-277V	32W	1900	140.7	G13	4100K	80	25	2
LT813B241KBP	LED 13.5W 4' T8 2E BYPASS 41K (BULK PACK)	*	13.5	120-277V	32W	1900	140.7	G13	4100K	80	25	1
LT813B250K	LED 13.5W 4' T8 2E BYPASS 50K (BULK PACK)	*	13.5	120-277V	32W	2000	148.1	G13	5000K	80	25	2
<b>LED 15.5 WATT ALL GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80415XXE)#</b>												
LT815B230K	LED 15.5W 4' T8 2E BYPASS 30K	*	15	120-277V	32W	1850	123.3	G13	3000K	80	25	1
LT815B235K	LED 15.5W 4' T8 2E BYPASS 35K	*	15	120-277V	32W	1900	126.6	G13	3500K	80	25	1
LT815B241K	LED 15.5W 4' T8 2E BYPASS 41K	*	15	120-277V	32W	1950	130	G13	4100K	80	25	1
LT815B250K	LED 15.5W 4' T8 2E BYPASS 50K	*	15	120-277V	32W	2000	133.3	G13	5000K	80	25	1
<b>LED 17 WATT ALL GLASS T8 TUBE – 4 FOOT (BULK PACK) (DLC LOOK UP T80407XXE)#</b>												
T8040730EBP	4' GLASS LED T8 Type B DE 30K (BULK PACK)	*	17	120-277V	32W	1750	103	G13	3000K	80	25	P
T8040735EBP	4' GLASS LED T8 Type B DE 35K (BULK PACK)	*	17	120-277V	32W	1800	106	G13	3500K	80	25	P
T8040741EBP	4' GLASS LED T8 Type B DE 41K (BULK PACK)	*	17	120-277V	32W	1850	109	G13	4100K	80	25	P
T8040750EBP	4' GLASS LED T8 Type B DE 50K (BULK PACK)	*	17	120-277V	32W	1850	109	G13	5000K	80	25	P
<b>LED 19 WATT ALL GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80491XXE)#</b>												
LT819B241K	LED 19W 4' T8 2E BYPASS 41K SC	*	19	120-277V	32W	2500	131.5	G13	4100K	80	25	2
LT819B250K	LED 19W 4' T8 2E BYPASS 50K SC	*	19	120-277V	32W	2500	131.5	G13	5000K	80	25	2
<b>LED 22 WATT ALL GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80495XXE)#</b>												
LT822B241K	LED 22W 4' T8 2E BYPASS 41K SC	*	22	120-277V	32W	2900	131.8	G13	4100K	80	25	2
LT822B250K	LED 22W 4' T8 2E BYPASS 50K SC	*	22	120-277V	32W	2900	131.8	G13	5000K	80	25	2
<b>LED 25 WATT ALL GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80490XXE)#</b>												
LT825B241K	LED 25W 4' T8 2E BYPASS 41K SC	*	25	120-277V	32W	3200	128	G13	4100K	80	25	2
LT825B250K	LED 25W 4' T8 2E BYPASS 50K SC	*	25	120-277V	32W	3200	128	G13	5000K	80	25	2
<b>LED 15 WATT ALL GLASS T8 TUBE – 4 FOOT 120-347V</b>												
LT815B230KC	LED 15W 4' T8 2E BY 347 30K		15	120-347V	32W	2200	146.6	G13	3000K	>80	25	2
LT815B235KC	LED 15W 4' T8 2E BY 347 35K		15	120-347V	32W	2200	146.6	G13	3500K	>80	25	2
LT815B241KC	LED 15W 4' T8 2E BY 347 41K		15	120-347V	32W	2200	146.6	G13	4100K	>80	25	2
LT815B250KC	LED 15W 4' T8 2E BY 347 50K		15	120-347V	32W	2200	146.6	G13	5000K	>80	25	2
<b>PLASTIC</b>												
<b>LED 17 WATT PLASTIC T8 TUBE – 4 FOOT (BULK PACK) (DLC LOOK UP T80414XXE)#</b>												
T8041430EBP	4' PLASTIC LED T8 Type B DE 30K (BULK PACK)	*	17	120-277V	32W	1750	103	G13	3000K	80	25	P
T8041435EBP	4' PLASTIC LED T8 Type B DE 35K (BULK PACK)	*	17	120-277V	32W	1800	106	G13	3500K	80	25	P
T8041441EBP	4' PLASTIC LED T8 Type B DE 41K (BULK PACK)	*	17	120-277V	32W	1800	109	G13	4100K	80	25	P
T8041450EBP	4' PLASTIC LED T8 Type B DE 50K (BULK PACK)	*	17	120-277V	32W	1850	109	G13	5000K	80	25	P

#XX Indicates CCT    <sup>1</sup> In Stock <sup>2</sup> Coming Soon <sup>P</sup> Phase Out



LED Ballast Bypass Double Ended T8 Tubes (cont.)

Item#	Description	DLC	LED Wattage	Voltage	Fluorescent Equivalency	Lumens	LPW	Base	CCT	CRI	Master Pack	Availability
<b>PET COATED GLASS</b>												
<b>LED 9 WATT PET COATED GLASS T8 TUBE – 2 FOOT (DLC LOOK UP L9T8BY50XXK)#</b>												
L9T8BY5030K	LED 9W 2' T8 BYPASS 30K	*	9	120-277V	17W	1125	125	G13	3000K	80	25	1
L9T8BY5035K	LED 9W 2' T8 BYPASS 35K	*	9	120-277V	17W	1125	125	G13	3500K	80	25	1
L9T8BY5041K	LED 9W 2' T8 BYPASS 41K	*	9	120-277V	17W	1200	133.3	G13	4100K	80	25	1
L9T8BY5050K	LED 9W 2' T8 BYPASS 50K	*	9	120-277V	17W	1250	138.8	G13	5000K	80	25	1
<b>LED 12 WATT PET COATED GLASS T8 TUBE – 3 FOOT</b>												
L12T8BY5030K	LED 12W 3' T8 BYPASS 30K		12	120-277V	25W	1200	100	G13	3000K	80	25	1
L12T8BY5035K	LED 12W 3' T8 BYPASS 35K		12	120-277V	25W	1200	100	G13	3500K	80	25	1
L12T8BY5041K	LED 12W 3' T8 BYPASS 41K		12	120-277V	25W	1200	100	G13	4100K	80	25	1
L12T8BY5050K	LED 12W 3' T8 BYPASS 50K		12	120-277V	25W	1200	100	G13	5000K	80	25	1
<b>LED 13 WATT PET COATED GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80415BXXE)#</b>												
L13T8BY5030K	LED 13.5W 4' T8 BYPASS 30K	*	13.5	120-277V	32W	1700	133.3	G13	3000K	80	25	1
L13T8BY5035K	LED 13.5W 4' T8 BYPASS 35K	*	13.5	120-277V	32W	1800	133.3	G13	3500K	80	25	1
L13T8BY5041K	LED 13.5W 4' T8 BYPASS 41K	*	13.5	120-277V	32W	1900	140.7	G13	4100K	80	25	1
L13T8BY5050K	LED 13.5W 4' T8 BYPASS 50K	*	13.5	120-277V	32W	2000	148.1	G13	5000K	80	25	1
<b>LED 19 WATT PET COATED GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80491XXE)#</b>												
LPT819B230K	LED 19W 4' T8 2E BYPASS 30K SC		19	120-277V	32W	2500	131.5	G13	3000K	80	25	2
LPT819B235K	LED 19W 4' T8 2E BYPASS 35K SC	*	19	120-277V	32W	2500	131.5	G13	3500K	80	25	2
LPT819B241K	LED 19W 4' T8 2E BYPASS 41K SC	*	19	120-277V	32W	2500	131.5	G13	4100K	80	25	2
LPT819B250K	LED 19W 4' T8 2E BYPASS 50K SC	*	19	120-277V	32W	2500	131.5	G13	5000K	80	25	2
<b>LED 22 WATT PET COATED GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80495XXE)#</b>												
LPT822B230K	LED 22W 4' T8 2E BYPASS 30K SC		22	120-277V	32W	2900	131.8	G13	3000K	80	25	2
LPT822B235K	LED 22W 4' T8 2E BYPASS 35K SC	*	22	120-277V	32W	2900	131.8	G13	3500K	80	25	2
LPT822B241K	LED 22W 4' T8 2E BYPASS 41K SC	*	22	120-277V	32W	2900	131.8	G13	4100K	80	25	2
LPT822B250K	LED 22W 4' T8 2E BYPASS 50K SC	*	22	120-277V	32W	2900	131.8	G13	5000K	80	25	2
<b>LED 25 WATT PET COATED GLASS T8 TUBE – 4 FOOT (DLC LOOK UP T80490XXE)#</b>												
LPT825B230K	LED 25W 4' T8 2E BYPASS 30K SC		25	120-277V	54W	3200	128.0	G13	3000K	80	25	2
LPT825B235K	LED 25W 4' T8 2E BYPASS 35K SC		25	120-277V	54W	3200	128.0	G13	3500K	80	25	2
LPT825B241K	LED 25W 4' T8 2E BYPASS 41K SC	*	25	120-277V	54W	3200	128.0	G13	4100K	80	25	1
LPT825B250K	LED 25W 4' T8 2E BYPASS 50K SC	*	25	120-277V	54W	3200	128.0	G13	5000K	80	25	1

RECOGNIZED COMPONENT



Intertek 4005203

#XX Indicates CCT

<sup>1</sup> In Stock <sup>2</sup> Coming Soon

APPLIES TO ALL TUBES ON THIS PAGE

CONFORMS TO NSF STD. 2