



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827

LTXES03BC 3/4"X100' LT Flex Metallic Conduit

Abb Installation Products, Inc



Catalog Number	LTXES03BC
Manufacturer	Abb Installation Products, Inc
Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core With TPR Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to Rohs, Black
Weight per unit	0.3900 (lbs/each)
Product Category	Liquid Tight Conduit

Features

Inside Diameter	0.82
outside diameter	1.05

Material, Color, and Finish

Color	Black
Finish	TPR Jacket

Dimensions and Weight

Length	1200
--------	------

Descriptions

Description	3/4"X100' LT FLEX METALLIC CONDUIT
extra long description	ABB LTXES03B-C LFMC XTMP 3/4IN BLK
Features	Extreme temperature, CE compliant Liquid-tight Flexible Metallic Conduits provide excellent performance in extreme low and high temperature environments
Long Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core with TPR Jacket, Conduit Size 3/4 Inch, Length 30 Meters/100 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to RoHS, Black
Product Type	LFMC XTMP 3/4IN BLK 30M/100FT
Special Features	Designed to meet UL 360 ID/OD dimension requirements

Manufacturer Information

Brand	T&B Liquidtight Systems
GTIN	00786210106700
Manufacturers Part Number	LTXES03B-C
UPC	786210106700



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquid Tight Flexible Metallic Conduit

Trade Size

Trade Size	3/4 in
------------	--------

Packaging

Carton	100
Weight Per each	0.39

Uses, Certifications, and Standards

Application	Used in extremely high temperature applications such as commercial ovens and refrigeration, industrial furnaces and foundries
standard	RoHS