



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PD3PCLWH Caseta 100W Led Plug-In White

Lutron

Catalog Number	PD3PCLWH
Manufacturer	Lutron
Description	Lutron Caseta Wireless Smart Lighting Lamp Dimmer
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Push-button
connection	Plug
Connection Type	Plug
insulation	Plastic
Material	Plastic/Metal
media	Yes
Switch Type	Push button
Voltage Rating	120

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	3.13 x 3.19;79.4 x 55.6
------	-------------------------

Descriptions

Description	CASETA 100W LED PLUG-IN WHITE
extra long description	LUT PD-3PCL-WH Caseta Lamp Dimmer
Features	Conveniently create just the right light for reading, watching TV, or entertaining, with the Lutron Caseta Wireless plug-in lamp dimmer. The plug-in lamp dimmer simply plugs into a standard outlet and can be used with up to two lamps. Control the lights from anywhere in the room by using the Pico remote control (sold separately). You can even add a wall switch to control plug-in lamps without running wires or cutting holes - using the Pico remote control with wall mounting kit (sold separately) and Caseta
Long Description	Lutron Caseta Wireless Smart Lighting Lamp Dimmer
Product Type	Caseta Lamp Dimmer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276072069
Manufacturers Part Number	PD-3PCL-WH
UPC	784276072069

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless plug-in lamp dimmer, single-pole

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	50 to 60
Operating Temperature	32 to 104