



# PENA4, Oxide Inhibitor, 4 ounce

By Burndy  
Catalog # [PENA4](#)

Oxide Inhibiting Electrical Joint Compound, 4 OZ, For Al-Al, Al-Cu & Al Conduit Threads.



### Application

Aluminum to Aluminum, Aluminum to Conduit, Aluminum to Copper

### General

Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810593103
UPC 12 Digit	7818105931033
Viscosity at 100 Fahrenheit	305 °F

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	12
Container Size	4 oz
Minimum Pack Quantity	1
Pallet Quantity	4032

### Product Assets

- [3D Models - PENA4\\_MODEL-STEP](#)
- [3D Models - PENA4\\_MODEL-PDF](#)
- [3D Models - PENA4\\_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - sc087700-01](#)
- [SDS - PENETROX\\_A\\_FRENCH\\_GHS](#)
- [SDS - PENETROX\\_A\\_GHS](#)
- [SDS - PENETROX\\_A\\_ESTONIAN\\_GHS](#)
- [SDS - PENETROX\\_A\\_PORTUGUESE\\_GHS](#)
- [SDS - PENETROX\\_A\\_ESPANOL\\_GHS](#)
- [SDS - PENETROX\\_A\\_GERMAN\\_GHS](#)



A proud member of the Hubbell Family.