

Eaton M22-DRH-X-SRG

Catalog Number: M22-DRH-X-SRG

Eaton M22 modular pushbutton M22 Modular Pushbutton Operator, 22.5 mm, Extended, Maintained, Non-illuminated, Bezel: Silver, Button: Black, red, green, IP67, IP69K, NEMA 4x, 13, 1,000,000 mechanical operations

General specifications



Photo is representative

Product Name

Eaton M22 modular pushbutton

UPC

786685276489

Product Height

1.5 in

Product Weight

0.04 lb

Catalog Number

M22-DRH-X-SRG

Product Length/Depth

7 in

Product Width

5 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

GoST-R
CE Marked
Bureau Veritas

Certifications

CCC Marked
CSA Certified
Lloyd's Register Certified

Catalog Notes

Includes contact block mounting adapter.
Buttonless operator, comes with three color buttons.

defaultTaxonomyAttributeLabel

Type

Pushbutton

Bezel

Silver

Actuator function

Maintained

Button color

Black, red, green

Actuator

Extended, button

Illumination

Non-illuminated

Series

M22

Environmental rating

IP67, IP69K, NEMA 4X, NEMA 13

Operating cycles

1 million

Size

22.5 mm

Resources

Brochures

[M22 Pilot Devices](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[M22\(S\)\(M\)-DRH 3D Inventor](#)

[M22\(S\)\(M\)-DRH AutoCAD 2D Footprint](#)

[M22\(S\)\(M\)-DRH 2D Drawing Xchange](#)

[M22\(S\)\(M\)-DRH 3D Model Xchange](#)

[M22\(S\)\(M\)-DRH AutoCAD 2D Footprint \(mm\)](#)

[M22\(S\)\(M\)-DRH 2D PDF](#)

Installation instructions

[M22 Operators and Accessories](#)

Specifications and datasheets

[Eaton Specification Sheet - M22-DRH-X-SRG](#)

[Global Data Sheet - M22-DRH-X-SRG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)