

Weight: 20.6 lbs

**Type:**

Date:


## LED Info

Type	Constant Current	Watts	100W
120V	0.88A	Color Temp	5000K (Cool)
208V	0.48A	Color Accuracy	74 CRI
240V	0.42A	L70 Lifespan	60,000 Hours
277V	0.38A	Lumens	15,899 lm
Input Watts	105.3W	Efficacy	151 lm/W

PIPXL100SF/D10



Dimensions



Features

- Ultra-high efficiency
- DLC Premium
- 0-10V Dimming, standard
- 60,000-Hour LED lifespan
- 5-Year, limited warranty

Ordering Matrix

Family	Wattage	Mount	Color Temp	Finish	Driver	Options	Other Options
PIPXL	100	SF			/D10		
100 = 100W 70 = 70W		SF = Slipfitter T = Trunnion	Blank = 5000K Cool N = 4000K Neutral Y = 3000K Warm	Blank = Bronze W = White	/480/D10 = Dimmable 480V /D10 = Dimmable 120-277V	Blank = No Options /PCU = 120-277V Button Photocell /PCT = 120-277V Twistlock photocell /PCT4 = 480V Twistlock photocell /7PR = 7-Pin Receptacle /BL = Bi-Level /LC = Lightcloud	Blank = Standard USA = BAA Compliant