

1-Gang



2-G	ang
-----	-----

Description	Material	Catalog No.	Colors		
1-Gang Box Mounted	Polycarbonate	□ PJ13	A, B, BK, GY, LA, V, W		
	REPEL Polycarbonate	DPJ13AM	GY, V, W	•	
	Thermoset	□ 2029	A, B, LA, V, W		
	302/304 Stainless Steel	□ 93951	_		
1-Gang Strap Mounted	Polycarbonate	□ PJ14	A, B, BK, GY, LA, V, W		
	REPEL Polycarbonate	DPJ14AM	GY, V, W	•	
2-Gang Box Mounted	Polycarbonate	□ PJ23	A, B, BK, GY, LA, V, W		
	REPEL Polycarbonate	DPJ23AM	GY, V, W	•	
	Thermoset	□ 2037	A, LA, V, W		•
2-Gang Strap Mounted	Polycarbonate	□ PJ24	A, B, BK, GY, LA, V, W		
	REPEL Polycarbonate	D PJ24AM	GY, V, W	•	





1-Gang with 0.406" Hole, Box Mounted



1-Gang with 0.406" Hole, Strap Mounted

**Telephone & Coax** <u>ال</u> Description Material Catalog No. Colors Thermoset 1-Gang with 0.37" □ 2028\_ V, W • (9.5mm) Hole 302/304 Stainless Steel □ 93996 • 1-Gang with 0.40" □ PJ11\_ A, B, BK, GY, LA, V, W Polycarbonate (10.3mm) Hole, Box Mounted 1-Gang with 0.40" □ PJ12\_ A, B, BK, GY, LA, V, W Polycarbonate (10.3mm) Hole, Strap Mounted

### **Color Ordering Information**

For ordering wallplates, include Cat. No. followed by the color code: A (Almond), B (Brown), BK (Black), BL (Blue), GY (Gray), LA (Light Almond), RD (Red), RN (Orange), V (Ivory), W (White)

Specification Information: *Wallplates: J-21* 



NAFTA Compliant - see page O-30
REPEL Wallplates - see page J-1

#### Certifications


PJ & PJS series wallplates are cULus certified 2000 series wallplates are cULus certified 90000 series wallplates are UL and CSA certified

www.arrowhart.com



# Mounting Holes for Wallplates and Covers


These are the most common nominal spacings for mounting holes on wallplates and covers. Holes are normally countersunk for oval head #6-32 screws.



# **Plate and Cover Opening Dimensions**

#### **Cover Openings**

Nominal dimensions for plate and cover openings conform to industry standards and practices.





3-Wire Power

Device



Single Locking

Receptacle


20/30 AMP



Single Receptacle


## **Common Opening Configurations**

Device







Description		Height	Width	First Gang to Edge	Gang to Gang
1-Gang	Standard	4.50" (114.3mm)	2.75" (69.8mm)	1.37" (34.9mm)	_
	Mid-Size	4.87" (123.8mm)	3.12" (79.4mm)	1.56" (39.7mm)	_
	Oversize	5.25" (133.3mm)	3.50" (88.9mm)	1.75" (44.4mm)	_
2-Gang	Standard	4.50" (114.3mm)	4.56" (115.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	4.94" (125.4mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.3mm)	5.31" (134.9mm)	1.75" (44.4mm)	1.81" (46.0mm)
3-Gang	Standard	4.50" (114.3mm)	6.37" (161.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	6.75" (171.4mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.4mm)	7.17" (182.2mm)	1.75" (44.4mm)	1.81" (46.1mm)
4-Gang	Standard	4.50" (114.3mm)	8.19" (207.9mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	8.56" (217.5mm)	1.56" (39.7mm)	1.81" (46.0mm)
	Oversize	5.25" (133.3mm)	8.94" (227.0mm)	1.75" (44.4mm)	1.81" (46.0mm)
5-Gang	Standard	4.50" (114.3mm)	10.00" (254.0mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	10.37" (263.5mm)	1.56" (39.7mm)	1.81" (46.0mm)
6-Gang	Standard	4.50" (114.3mm)	11.81" (300.0mm)	1.37" (34.9mm)	1.81" (46.0mm)
	Mid-Size	4.87" (123.8mm)	12.18" (309.5mm)	1.56" (39.7mm)	1.81" (46.0mm)







#### Standard





# Wallplates

Standard Size Mid-Size Oversize REPEL

	Wallplate Type		Standard Siz & Oversize		REPEL		
	Material Type	Thermoset	Nylon	Stainless Steel	Polycarbonate	REPEL Polycarbonate Mid-Sized Wallplates PJ_AM and PJS_AM Series	REPEL Stainless Steel Standard Size Wallplates 93070_AM, 93090_AM, 93100_AM, 93400_AM Series
	Manufacturing Process	Injection Molded	Injection Molded	Stamped	Injection Molded	Injection Molded	Stamped
		UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E33216	UL Listed to 514D, file no. E92003	UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E33216	UL Listed to UL 514D, file no. E92003
	Testing & Code Compliance	et cult certified to C22.2, no. 42.1,	cUL certified to C22.2, no. 42.1,	CSA certified to C22.2, no. 42.1	cUL, UL file E33216 certified to C22.2, no. 42.1	Agion <sup>®</sup> Antimicrobial Additive: EPA approved for use as product ingredient	Agion <sup>®</sup> Antimicrobial Additive: EPA approved for use as product ingredient
		UL file E33216	UL file E33216			PJ_AM only: cUL Listed to CSA C22.2, no 42.1, file no. E33216	CSA certified to C22.2, no. 42.1
ations: mental	Flammability	Meets UL 94 requirements; 5V rated	Meets UL 94 requirements; 5V rated	N/A	Meets UL 94 requirements 5VA rated	Meets UL 94 requirements; 5V rated	N/A
Specifications: Environmental	Temperature Rating	-40°C to 90°C (-40°F to 194°F)	-40°C to 70°C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)	-40° to 70° C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)	-40°C to 70°C (-40°F to 158°F)
Materials:	Body	0.080" thick thermoset urea or phenolic	0.060" thick thermoplastic	0.032" thick stainless steel alloy, 18% chromium and 8% nickel for corrosion resistance	0.08" thick thermoplastic polycarbonate	0.071" thick polycarbonate with Agion® Antimicrobial Additive incorporated	0.032" thick 302/304 stainless steel alloy, 18% chromium and 8% nickel for corrosion resistance, DuPont® Alesta® powder coating with Agion® Antimicrobial incorporated
	Inner Wallplate	N/A	N/A	N/A	0.071" thick polycarbonate	PJS_AM only: 0.071" thick polycarbonate	N/A

NOTE: REPEL products do not protect the user against disease causing organisms and ongoing regular cleaning practices should be maintained. Agion is a registered trademark of Agion Technologies, Inc., Wakefield, MA