Duraclad® Type MC



14 AWG through 6 AWG Copper THHN/THWN Insulated Singles. Green Copper THHN Insulated Grounding Conductor. UL Listed. 600 Volts. Rated VW-1. Lightweight Steel Interlocked Armor. Also available in Blue Steel Armor.

APPLICATIONS

Southwire Duraclad® Type MC Cable is suitable for use as follows:

- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Environmental air-handling spaces per NEC 300.22(C).
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5.
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC 645.5(D) & 645.5(D)(2).
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations.

STANDARDS & REFERENCES

Southwire Duraclad® Type MC Cable meets or exceeds the following requirements:

- UL 83
- UL 1569
- UL 1685
- UL Online Product Guide Info Metal-Clad Cable (PJAZ) (www.ul.com)
- Federal Specification A-A-59544
- NFPA 70 (National Electrical Code), Article 330
- Jacketed & Non Jacketed will both pass "UL Test" & "FT4/IEEE 1202" (70,000 Btu/hr) Vertical Cable Tray Flame Test
- Listed for use in UL 1, 2, and 3 Hour Through-Penetration Firestop Systems
- REACH/RoHS-2 (Chemical Limit) Compliant

CONSTRUCTION

Southwire Duraclad Type MC Cable is constructed with soft-drawn copper, Type THHN/THWN conductors and a green insulated grounding conductor. The conductors are cabled together and a binder tape bearing the print legend is wrapped on the assembly. Light weight galvanized steel interlocked armor is applied over the assembly. Blue steel armor is also available.





Duraclad Type MC - Lightweight Steel Armor

CONDUCTOR SIZE AND COLORS	GROUNDING SIZE AND COLOR	STOCK NUMBER		WEIGHT	OVERALL		
		COIL (250')	REEL (1000')	(LBS/1000')	DIAMETER (INCHES)		
SOLID CONDUCTOR COLORS 120/208V							
14-2 SOLID (BLACK/WHITE)	14 SOLID (GREEN)	55-17-15-01	55-17-15-02	115	.447		
14-3 SOLID (BLACK/WHITE/RED)	14 SOLID (GREEN)	55-17-28-01	55-17-28-02	138	.464		
14-4 SOLID (BLACK/WHITE/RED/BLUE)	14 SOLID (GREEN)	55-17-33-01	55-17-33-02	154	.502		
12-2 SOLID (BLACK/WHITE)	12 SOLID (GREEN)	55-17-16-01	55-17-16-02	142	.475		
12-3 SOLID (BLACK/WHITE/RED)	12 SOLID (GREEN)	55-17-29-01	55-17-29-02	172	.513		
12-4 SOLID (BLACK/WHITE/RED/BLUE)	12 SOLID (GREEN)	55-17-34-01	55-17-34-02	201	.547		
10-2 SOLID (BLACK/WHITE)	10 SOLID (GREEN)	55-17-17-01	55-17-17-02	197	.550		
10-3 SOLID (BLACK/WHITE/RED)	10 SOLID (GREEN)	55-17-30-01	55-17-30-02	240	.588		
10-4 SOLID (BLACK/WHITE/RED/BLUE)	10 SOLID (GREEN)	55-17-35-01	55-17-35-02	284	.631		
STRANDED CONDUCTOR COLORS 120/208V							
12-2 STRANDED (BLACK/WHITE)	12 STRANDED (GREEN)	55-64-36-01	55-64-36-02	157	.495		
12-3 STRANDED (BLACK/WHITE/RED)	12 STRANDED (GREEN)	55-36-32-01	55-36-32-02	187	.527		
10-2 STRANDED (BLACK/WHITE)	10 STRANDED (GREEN)		55-39-67-02	213	.566		
10-4 STRANDED (BLACK/WHITE/RED/BLUE)	10 STRANDED (GREEN)		56-10-24-02	307	.653		
	SOLID CONDUC	TOR COLORS 27	7/480V				
12-2 SOLID (BROWN/GRAY)	12 SOLID (GREEN)	55-17-74-01		142	.475		
12-2 SOLID (ORANGE/GRAY)	12 SOLID (GREEN)	55-32-42-02	55-32-42-03	142	.475		
12-3 SOLID (BROWN/YELLOW/GRAY)	12 SOLID (GREEN)	55-32-51-02	55-32-51-03	172	.513		
12-4 SOLID (BROWN/ORANGE/YELLOW/GRAY)	12 SOLID (GREEN)	55-32-44-02	55-32-44-03	201	.547		
10-2 SOLID (ORANGE/GRAY)	10 SOLID (GREEN)	55-17-83-01	55-17-83-02	197	.550		
10-2 SOLID (YELLOW/GRAY)	10 SOLID (GREEN)	55-17-82-01	55-17-82-02	197	.550		
10-2 SOLID (BROWN/GRAY)	10 SOLID (GREEN)	55-32-50-02	55-32-50-03	197	.550		
10-3 SOLID (BROWN/ORANGE//GRAY)	10 SOLID (GREEN)	55-32-52-02	55-32-52-01	240	.588		
10-3 SOLID (BROWN/YELLOW/GRAY)	10 SOLID (GREEN)	55-17-87-01	55-17-87-02	240	.588		
10-4 SOLID (BROWN/ORANGE/YELLOW/GRAY)	10 SOLID (GREEN)	55-32-45-02	55-32-45-01	284	.631		



Duraclad Type MC - Lightweight Steel Armor

FEATURES

- Reduces installation costs up to 50% over pipe and wire.
- UL Classified 1, 2, and 3 hour Through Penetration Firestop Systems: W-J-3037, W-L-3110, W-L-3113, W-L-3117, W-L-3120, W-L-3121, W-L-3160, C-AJ-3115, C-AJ-3140, C-AJ-3142, C-AJ-3145, C-AJ-3173, C-AJ-3202, C-AJ-4065, C-AJ-4066, F-C-3038.
- Cable reverse wound on reel for ease of pulling and installation. When pulling from coils, pull from inside to ensure ease
 of installation.
- Anti-short bushings are not required for use with MC cable per the NEC and UL
- Available in stranded conductors.

NEC TABLE 310.15(B)(16)- ALLOWABLE AMPACITY FOR 600V CONDUCTORS

	TEMPERATURE RATING OF CONDUCTOR				
	60°C (140°F)	75°C (167°F)	90°C (194°F)		
SIZE AWG OR KCMIL	Types: TW, UF	Types: RHW, THHW, THW, THWN, XHHW, USE, ZW	Types: TBS, SA, SIS, RHH, RHW-2, THHN, THHW, THW-2, THWN- 2, USE-2, XHH, XHHW, XHHW-2, ZW-2		
	COPPER				
18	-	-	14		
16	-	=	18		
14	15	20	25		
12	20	25	30		
10	30	35	40		
8	40	50	55		
6	55	65	75		
4	70	85	95		
3	85	100	115		
2	95	115	130		
1	110	130	145		
1/0	125	150	170		
2/0	145	175	195		
3/0	165	200	225		
4/0	195	230	260		
250	215	255	290		
300	240	285	320		
350	260	310	350		
400	280	335	380		
500	320	380	430		
600	350	420	475		
700	385	460	520		
750	400	475	535		
800	410	490	555		
900	435	520	585		
1000	455	545	615		
1250	495	590	665		
1500	525	625	705		
1750	545	650	735		
2000	555	665	750		
Per NEC 310.15(B)(5), the ampacity of 4/C cables shall be reduced by a					

Per NEC 310.15(B)(5), the ampacity of 4/C cables shall be reduced by a factor of 0.80 when the neutral is considered a current-carrying conductor.

Table is reprinted from NFPA 70-2014, the National Electric Code, © 2013 National Fire Protection Association, Quincy, Massachusetts 02269. This reprinted material is not the complete and official position of the National Fire Protection Association on the referenced subject, which is represented only by the standard in its entirety.

