

Rugged Design and Quality Materials Make Arrow Hart Wallplates the Best Choice

Whether faced with a commercial, institutional or industrial setting, you will find the desired material, configuration, style, size and color you need



Standard Size
wallplates for precision cuts



Mid-Size and Oversize
wallplates for applications that require additional wall coverage



Extra Depth
wallplates to provide a flush fit to the wall when an old work outlet box is used



Specification Grade Thermoplastic

- Available in both Nylon and Polycarbonate constructions
- Virtually unbreakable plates reduce installation and replacement costs
- Preferred for industrial, institutional, and other high-traffic areas
- Exclusive timesaving Screw-Catch™ feature holds mounting screws captive and simplifies installation
- High gloss finish is soil-resistant
- Available in Standard Size and Mid-Size configurations with screwless and Pre-Marked Special Use versions available



Specification Grade Metal Wallplates

- Constructed of non-corrosive 302/304 Stainless Steel, Brass, or Chrome
- Available in Standard, Mid-Size, and Oversize configurations with Pre-Marked Special Use versions available
- 302/304 Stainless is non-magnetic and non-corrosive for rugged durability
- Solid brass is coated with transparent lacquer to resist premature oxidation
- Shipped with removable protective film
- Recommended for industrial, institutional, and commercial applications

Same Style, Same Durable Quality Now With CuVerro® Antimicrobial Copper Surfaces

The Arrow Hart™ line of devices featuring CuVerro® Antimicrobial Copper Surfaces, offer specification grade decorator switches and wallplates in multiple gangs and configurations

Features & Benefits

CuVerro®

Antimicrobial Copper Surfaces

Wallplates with CuVerro®
Antimicrobial Touch Surface



- 1 Touch surfaces constructed of EPA registered** CuVerro® Antimicrobial Copper
- 2 When cleaned regularly, delivers continuous and ongoing antibacterial* action, remaining effective in killing greater than 99.9% of bacteria* within 2 hours
- 3 Unlike coatings, CuVerro® surfaces are wear resistant and the durable antibacterial* properties will remain effective for as long as the product remains in place and is used as directed
- 4 Tarnish resistant with minimal color change over time
- 5 Surfaces should be cleaned to regular protocols
- 6 Durable enough for hospital grade cleaners

Antimicrobial Copper **Cu⁺**

+Laboratory testing shows that, when cleaned regularly, CuVerro® antimicrobial copper surfaces kill greater than 99.9% of the following bacteria within 2 hours of exposure: MRSA, Staphylococcus aureus, Enterobacter aerogenes, Pseudomonas aeruginosa, and E. coli O157:H7. CuVerro® antimicrobial copper surfaces are a supplement to and not a substitute for standard infection control practices and have been shown to reduce microbial contamination, but do not necessarily prevent cross contamination; users must continue to follow all current infection control practices, including those practices related to cleaning and disinfection of environmental surfaces. CuVerro® is a registered trademark of GBC Metals, LLC and is used with permission, CW-0013-1207.

**EPA Registration Number 85353-5 (7600CUR Series) and 85353-3 (7600CU Series)
Specifications and availability are subject to change without notice.

Mid-Size Wallplates Toggle Switch


1-Gang, 2-Gang, 3-Gang,
4-Gang, 5-Gang, 6-Gang

Toggle Switch


| Gang | Material | Color Suffix | Catalog No. | |
|--------|-------------------------|----------------------------|-------------|---|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ1__ | |
| | Thermoset | A, B, LA, V, W | □ 2034__ | • |
| | 302/304 Stainless Steel | — | □ 93971 | • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ2__ | |
| | Thermoset | A, B, LA, V, W | □ 2039__ | • |
| | 302/304 Stainless Steel | — | □ 93972 | • |
| 3-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ3__ | |
| | Thermoset | A, LA, V, W | □ 2041__ | • |
| | 302/304 Stainless Steel | — | □ 93973 | • |
| 4-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ4__ | |
| | Thermoset | A, LA, V, W | □ 2054__ | • |
| 5-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ5__ | |
| 6-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ6__ | |




1-Gang




2-Gang




3-Gang




4-Gang




5-Gang



6-Gang



1-Gang



2-Gang

Mid-Size Wallplates Duplex & Single Receptacle


1-Gang, 2-Gang

Duplex Receptacle

| Gang | Material | Color Suffix | Catalog No. | |
|--------|-------------------------|----------------------------|-------------|---|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ8__ | |
| | Thermoset | A, B, LA, V, W | □ 2032__ | • |
| | 302/304 Stainless Steel | — | □ 93901 | • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ82__ | |
| | Thermoset | A, LA, V, W | □ 2050__ | • |
| | 302/304 Stainless Steel | — | □ 93902 | • |

Duplex Receptacle

| Gang | Material | Color Suffix | Catalog No. | |
|------------------------------------|-------------------------|----------------|-------------|---|
| 1-Gang with 1.406" (35.712mm) Hole | Thermoset | A, B, LA, V, W | □ 2031__ | • |
| | 302/304 Stainless Steel | — | □ 93991 | • |



1-Gang

Color Ordering Information:

For ordering devices, include Catalog No. followed by the Color Suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Certification Information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are only UL Listed. **Specification Information:** L-22
Specifications and availability are subject to change without notice.

Indicates NAFTA Compliant - Page R-30

Wallplates | Standard Size, Mid-Size, Oversize

| Wallplate Sizes: Standard Size, Mid-Sized & Oversize Wallplates | | | | | | Wallplate Size: Standard Size |
|---|---|---|------------------------------------|---|--|--|
| Material Type | Thermoset | Nylon | Stainless Steel | Polycarbonate | CuVerro® Antimicrobial Copper Surfaces* | |
| | Injection Molded | Injection Molded | Stamped | Injection Molded | Stamped | |
| Testing & Code Compliance | UL Listed to UL 514D, file no. E33216 | UL Listed to UL 514D, file no. E33216 | UL Listed to 514D, file no. E92003 | UL Listed to UL 514D, file no. E33216 | UL Listed to UL514D, file no. E92003 | |
| | cUL Listed to C22.2, no. 42.1, UL file E33216 | cUL Listed to C22.2, no. 42.1, UL file E33216 | CSA certified to C22.2, no. 42.1 | cUL, UL file E33216 certified to C22.2, no. 42.1 | CuVerro® Antimicrobial Copper EPA Registration Number 85353-5 (9000CUR series) and 85353-3 (9000CU series) | |
| Environmental Specifications: | Flammability | Meets UL94 requirements; 5VA rated | Meets UL94 requirements; 5VA rated | N/A | Meets UL94 requirements 5VA rated | N/A |
| | Temperature Rating | -40°C to 90°C (-40°F to 194°F) | -40°C to 70°C (-40°F to 158°F) | -40°C to 70°C (-40°F to 158°F) | -40° to 70° C (-40°F to 158°F) | -40°C to 70°C (-40°F to 158°F) |
| Materials: | Body | 0.080" thick thermoset urea or phenolic | 0.060" thick thermoplastic | 0.032" thick stainless steel alloy, 18% chromium and 8% nickel for corrosion resistance | 0.08" thick thermoplastic polycarbonate | 0.040" thick CuVerro® Antimicrobial Copper Alloy, 99.5% containing copper, nickel, iron, manganese, zinc, and 0.05% lead |
| | Inner Wallplate | N/A | N/A | N/A | 0.071" thick polycarbonate (PJS Series) | N/A |

Footnote:

+Laboratory testing shows that, when cleaned regularly, CuVerro® antimicrobial copper surfaces kill greater than 99.9% of the following bacteria within 2 hours of exposure: MRSA, Staphylococcus aureus, Enterobacter aerogenes, Pseudomonas aeruginosa, and E. coli O157:H7. CuVerro® antimicrobial copper surfaces are a supplement to and not a substitute for standard infection control practices and have been shown to reduce microbial contamination, but do not necessarily prevent cross contamination; users must continue to follow all current infection control practices, including those practices related to cleaning and disinfection of environmental surfaces. CuVerro® is a registered trademark of GBC Metals, LLC and is used with permission, CW-0013-1207.