The Halo ML56 LED Downlighting System is a series of modular LED Modules for use with designated 5" or 6" ML56 LED trims in new construction, remodel and retrofit installation. Compatible with Halo 5" H550 and 6" H750, H2750 Series LED housings. And in retrofit of existing housings the ML56 Series fits 5" or 6" Halo and others. ML56 LED Modules are offered in 600 Series, 900 Series, and 1200 Series, 90CRI, and four color temperatures 2700K, 3000K, 3500K, 4000K. ML56 LED Modules are universal voltage 120V - 277V and dimmable at 120V. The ML56 lens provides uniform diffuse illumination standard.

Catalog #	Туре
During	
Project	
Comments	Date
Prepared by	

Specification Features

Mechanical

Light Module

- Module includes LED package, LED driver, heat sink, and lens
- Durable die-cast aluminum construction.
- Heat sink designed to conduct heat away from the LED keeping the junction temperatures below specified maximums, including insulated ceiling environments

- Impact-resistant polycarbonate
- Convex form for lamp-like appearance
- High lumen transmission
- Diffusing for even illumination

Mounting

- Modules attach to reflector and baffle trims via locking tabs, and attach to eyeballs via keyed twist-to-lock mating
- The complete module and trim assembly installs into housings with precision formed torsion springs located on the trim
- · Friction Blade mounting is an alternate option using the accessory 6" Friction Blade Kit model ML56CLIP (order separately). Friction blades provide alternative to torsion springs for retrofit in 6" housings without torsion mounting tabs. ML56CLIP is compatible with 6" baffle and reflector trims only (691, 692, 693, 695, 696 series). For eyeball trim (694 series) use ML7RAB retrofit adapter band.

Housing Compatibility

A complete ML56 system includes a LED Module, LED trim, and a compatible housing (new construction, remodel, or existing retrofit). Housing compatibility in the ML56 System is determined by the ML56 trim dimensions. ML56 trims are available in 5" and 6" aperture (5" = 59xx series and 6" = 69xx series trims). Refer to Housing - Trim Section in this document.

LED

- 600 Series = 600 design lumens typical
- Delivered lumens vary depending upon 5" or 6", color temperature, and trim finish.
- Color Temperature options: 2700K, 3000K, 3500K, 4000K

- CRI: 90 R9>50
- L70 at 50,000 hours, projected in accordance with IES TM-21
- LED is a chip on board design consisting of a multiple LED package to create one virtual light source for a productive "cone

Color Specification & Quality Standards

- A tight chromaticity specification ensures LED color uniformity, sustainable Color Rendering Index (CRI) and Correlated Color Temperature (CCT) over the useful life of
- LED color uniformity of 3 SDCM exceeds ENERGY STAR® color standards per ANSI C78.377- 2008.
- High color performance with 90CRI minimum, and R9 greater than 50.
- Every Halo LED Module is quality tested and performance measured, and then serialized in a permanent record to register lumens, wattage, CRI and CCT.
- · Halo LED serialized testing and measurement process ensures color and lumen consistency on a per-unit basis, and validates long-term product consistency
- Halo ML56 LED Modules include lumen, CRI, and CCT designations in the model number

Example: ML5606930

56 = 5'' / 6'' aperture series **06** = 600 lumen series

9 = >90 CRI

30 = 3000K nominal CCT

Electrical Power Connections

- · LED connector is a non-screw base luminaire disconnect offering easy installation with the matching Halo 5" H550 series and 6" H750 and H2750 series housings (housing selected depends upon LED trim 5" or 6")
- · LED Connector meets high-efficacy luminaire requirement for a non-screw base, and where required.
- The included E26 medium screw-base Edison adapter*provides easy retrofit of incandescent housings (see Housing

Ground Connection

Separate grounding cable included on the module for attachment to the housing during installation

LED Driver

- · Driver is universal voltage 120V-277V, and may be controlled from a switch in this range of main inputs (switchable at 120V, 220V, 230V, 240V, and 277V)
- · Driver is dimmable at 120V operation when connected to a compatible dimmer.
- Driver is a high efficiency, electronic power supply providing DC power to the LED.
- · Driver meets FCC EMI/RFI Consumer Level limits on 120V main inputs, and is compliant for use in residential and commercial installations.
- · Driver features high power factor, low THD, and has integral thermal protection in the event of over temperature or internal
- Driver is replaceable, if replacement should be required.

Dimming

Designed for dimming capability to nominal 5% in normal operation with standard 120V Leading Edge (LE) and Trailing Edge (TE) phase control dimmers (Consult dimmer manufacturer for dimmer compatibility and details. Note, some dimmers require a neutral in the wallbox.)

Warranty

Cooper Lighting Solutions provides a (5) five year limited warranty on the Halo ML56 LED Module

LED Module in New or Retrofit Existing Construction - Housings other than Halo

- · If used in recessed housings other than Halo the Cooper Lighting Solutions 5-year limited warranty applies to the LED Light Module and Trim only.
- · As with any electrical installation, a qualified electrician must ensure compatibility of use with a particular housing; this includes all applicable national and local electrical and building codes. Installer is responsible to properly and securely retain the LED Module and LED Trim in the housing at time of installation



System

600 Series / 90 CRI

ML5606927 ML5606930 ML5606935 ML5606940

5-Inch and 6-Inch 600 Lumen LED Module for New Construction. **Remodel and Retrofit**

For use with 59x and 69x **Series Trims**

FOR USE IN **INSULATED CEILING** AND NON-INSULATED **CEILING RATED** HOUSINGS

HIGH EFFICACY LED WITH INTEGRAL **DRIVER - DIMMABLE**

Energy Data

ML56 600/90 Series

(Values at non-dimming line voltage)

Minimum Starting Temp: -30°C (-22°F)

EMI/RFI: FCC Title 47 CFR, Part 15, (Consumer)

Sound Rating: Class A

Input Voltage: UNV 120V-277V

Power Factor: >0.95 @ 120V and >0.9 @277V

Input Frequency: 50/60Hz

THD: <20%

Innut Power: 9.5W

Input Current at 120V: 0.15A

Input Current at 277V: 0.08A

Driver Compliance: UL8750, Class II rated

Maximum IC (Insulated Ceiling) Ambient Continuous Operating Temperature: 25°C (77°F)

Maximum Non-IC Ambient Continuous Operating Temperature: 40°C (104°F)



ML5606927

5" or 6" LED 600 Series



5" or 6" LED 600 Series



5" or 6" LED 600 Series









Compliance

- · cULus listed 1598 Luminaire (Halo housings)
- . UL Classified when used in retrofit (refer to housing section)
- · cULus listed for damp locations
- cULus Wet location listed with baffle and reflector trims only
- Airtight certified per ASTM E283 (not exceeding 2.0 CFM under 57 Pascals pressure difference)
- IP66 ingress protection rated with baffle and reflector trims only
- · RoHS compliant

- May be used in IC (insulated ceiling) housings in direct contact with insulation* and combustible material
- Can be used for California Title 24 compliance
- Can be used for International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- Can be used for Washington State Energy Code compliance
- ENERGY STAR® certified luminaire consult ENERGY STAR® Certified product list
- EMI/RFI per FCC 47CFR Part 15 Class B Consumer limits (commercial and residential compliant)
- · Photometric testing in accordance with IES LM-79
- Lumen maintenance projections in accordance with IES LM-80 and TM-21
- CE Mark "Conformité Européene" conformity with the Council of European Communities Directives, meeting internationally recognized compliance when used with Halo H550, H750, and H2750 Series LED housings only
- Not for use with housings in direct contact with spray foam insulation.












Refer to ENERGY STAR® Qualified Products List. Can be used to comply with California Title 24 High Efficacy requirements.








Dimensions







Ordering Information

Sample Number: ML5606930 593WB

Order LED Module and trim separately

A complete system also includes a compatible housing (new construction, remodel, or existing retrofit). Housing aperture size in the ML56 System is determined by the ML56 trim dimensions. ML56 trims are available in 5" and 6" aperture (5" = 59xx series and 6" = 69xx series trims). Refer to Housing Section in this document.

ML56 LED Modules 600 Series / 90 CRI

ML5606927= 5"/6" LED module, 600 lumen, 90CBL 2700K

ML5606930= 5"/6" LED module, 600 lumen, 90CRI, 3000K

ML5606935= 5"/6" LED module, 600 lumen, 90CRI, 3500K

ML5606940= 5"/6" LED module, 600 lumen, 90CRI, 4000K

ML5606D2W930= 5"/6" dim-to-warm LED module, 600 lumen, 90CRI, 1850K

California non-E26 modules¹

ML5606927-CA= 5/6" LED module, 600 lumen, 90CRI, 2700K, California non-E26 ML5606930-CA= 5/6" LED module, 600 lumen, 90CRI, 3000K, California non-E26 ML5606935-CA= 5/6" LED module, 600 lumen, 90CRI, 3500K, California non-E26 ML5606940-CA= 5/6" LED module, 600 lumen, 90CRI, 4000K, California non-E26

ML56 LED 5" and 6" Trims

590 Series - 5" LED Trims

591WB=5" LED trim, polymer "dead-front", shallow white baffle & flange – shallow and standard housings (For use with 600 Series LED light modules only)

592SC=5" LED trim, specular reflector & white flange **592H**=5" LED trim, haze reflector & white flange

592W=5" LED trim, white reflector & flange

593WB=5" LED trim, white micro-step baffle & flange

593BB=5" LED trim, black micro-step baffle & white flange

593SNB=5" LED trim, satin nickel micro-step baffle & flange

593TBZB=5" LED trim, tuscan bronze micro-step baffle & flange **594WB**=5" LED directional trim, white eyeball, baffle & flange –

shallow and standard housings

594SNB=5" LED directional trim, satin nickel eyeball, baffle & flange – shallow and standard housings

594TBZB=5" LED directional trim, tuscan bronze eyeball, baffle & flange – shallow and standard housings

595WW=5" LED trim, wall wash - specular reflector, repositionable specular kick reflector, white flange

596WB=5" LED trim, white shallow baffle & flange - shallow and standard housings

690 Series - 6" LED Trims

691WB=6" LED trim, polymer "dead-front", white shallow baffle & flange – shallow and standard housings (For use with 600 Series LED light modules only)

692SC=6" LED trim, specular reflector & white flange

692H=6" LED trim, haze reflector & white flange

692W=6" LED trim, white reflector & flange

693WB=6" LED trim, white micro-step baffle & flange

693BB=6" LED trim, black micro-step baffle & white flange

693SNB=6" LED trim, satin nickel micro-step baffle & flange **693TBZB**=6" LED trim, tuscan bronze micro-step baffle & flange

694WB=6" LED directional trim, white eyeball, baffle & flange –

shallow and standard housings

694SNB=6" LED directional trim, satin nickel eyeball, baffle & flange –

shallow and standard housings

694TBZB=6" LED directional trim, tuscan bronze eyeball, baffle & flange –

shallow and standard housings

 $\textbf{695WW} \hbox{=} 6 \text{" LED trim, wall wash - specular reflector, repositionable specular}$

kick reflector, white flange

696WB=6" LED trim, white shallow baffle & flange – for use with shallow and standard housings

standard nousings

ML56 System Accessories

ML56CLIP=Friction clip mounting kit - For retrofitting non-torsion spring housings. 6" clips*

WW595SC=5" Wall wash insert - kick reflector for 595WW (1-included with trim) double or corner wall wash**

WW695SC=6" Wall wash insert - kick reflector for 695WW (1-included with trim) double or corner wall wash**

TRM590WH=5" LED oversize trim ring for use with 59* series trims, white 6.3" I.D., 7.5" O.D. Ring slips over LED trim. Inset design allows 5" trim to fit into oversize ring for an even trim surface

TRM690WH=6" LED oversize trim ring for use with 69* series trims, white 6.9" I.D., 9.5" O.D. Ring slips over LED trim. Inset design allows 6" trim to fit into oversize ring for an even trim surface

*ML56CLIP is compatible with 6" baffle and reflector trims only (691, 692, 693, 695, 696 series). For eyeball trim (694 series) use ML7RAB retrofit adapter band.

**Wall wash trims 595WW and 695WW Feature an exclusive repositionable kick reflector for fine-tuning adjustment of the wall wash effect. The WW595SC and WW695SC are repositionable kick reflectors sold separately for addition to the wall wash trim when a double or corner wall wash is needed, or for replacement of original kick reflector included with the trim.


Notes: 1. California product only.

Lighting Info


ML5606927

PRODUCT SPECIFICATIONS Lumens (Light Output) 714 Watts 9.5 Lumens Per Watt (Efficacy) 74.7 Color Accuracy (CRI) 92 Light Color (CCT) 2700K Orrelated Color Temperature (CCT) 2700K Soft Warm White White 2700K 3000K 4500K 6500K


ML5606930



ML5606935



ML5606940





Housing - Trim Compatibility

Housing compatibility in the ML56 System is determined by the ML56 trim dimensions. ML56 trims are available in 5" and 6" aperture (5" = 59xx series and 6" = 69xx series trims). Refer to ML56 TRIMS in this document. (Note "X" in the trim model number denotes finish code.)

Housing – Compatibility

The ML56 LED module - trim combination is cULus Listed or UL Classified for use with any 5" or 6" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 115 in³ in addition to those noted below.

Halo and All-Pro UL Listed Compatibility

6" Trims: 691X, 692X, 693X, 694X, 695X, 696X

(Note shallow housings for use with 691X, 694X, 696X trims only)

HALO - LED Housings with LED Luminaire Connector - High-Efficacy Compliant

Brand	Housing Type	Catalog Number	Description
Halo	Standard Housings	H750ICAT	6" LED, Insulated Ceiling, Air-Tite, New Construction Housing
		H750RICAT	6" LED, Insulated Ceiling, Air-Tite, Remodel Housing
		H750T	6" LED, Non-IC, Air-Tite, New Construction Housing
		H750TCP	6" LED, Non-IC, New Construction/Remodel Chicago Plenum Housing
		E750ICAT	6" LED, Insulated Ceiling, Air-Tite, New Construction Housing
		E750RICAT	6" LED, Insulated Ceiling, Air-Tite, Remodel Housing
Halo	Shallow Housings	H2750ICAT	6" LED, Shallow, Insulated Ceiling, Air-Tite, New Constr. (use with 691X, 694X, 696X trims only)
		H2750RICAT	6" LED, Shallow, Insulated Ceiling, Air-Tite, Remodel (use with 691X, 694X, 696X trims only)

HALO - Incandescent E26 Screwbase Housings

Brand	Housing Type	Catalog Number	Description
Halo	Standard Housings	H7ICAT	6" Insulated Ceiling, Air-Tite New Construction Housing
		H7RICAT	6" Insulated Ceiling, Air-Tite Remodel Housing
		H7ICT	6" Insulated Ceiling, New Construction Housing
		H7RICT	6" Insulated Ceiling, Remodel Housing
		H7ICATNB	6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket
		H7ICTNB	6" Insulated Ceiling, New Construction Housing, No Socket Bracket
		H7T	6" Non-IC, New Construction Housing
		H7RT	6" Non-IC, Remodel Housing
		H7TNB	6" Non-IC, New Construction Housing, No Socket Bracket
		H7TCP	6" Non-IC, Chicago Plenum, New Construction/Remodel Housing
		H7UICAT	6" Insulated Ceiling, Universal, Air-Tite, New Construction Housing
		E7ICAT	6" Insulated Ceiling, Air-Tite New Construction Housing
		E7RICAT	6" Insulated Ceiling, Air-Tite Remodel Housing
		E7ICATNB	6" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket
		E7TAT	6" Non-IC, Air-Tite New Construction Housing
		E7RTAT	6" Non-IC, Air-Tite Remodel Housing
		E7TATNB	6" Non-IC, Air-Tite New Construction Housing, No Socket Bracket
Halo	Shallow Housings	H27ICAT	6" Shallow, Insulated Ceiling, Air-Tite New Construction (use with 691X, 694X, 696X trims only)
		H27RICAT	6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing (use with 691X, 694X, 696X trims only)
		H27T	6" Shallow, Non-IC, New Construction Housing (use with 691X, 694X, 696X trims only)
		H27RT	6" Shallow, Non-IC, Remodel Housing (use with 691X, 694X, 696X trims only)
		E27ICAT	6" Shallow, Insulated Ceiling, Air-Tite New Construction (use with 691X, 694X, 696X trims only)
		E27RICAT	6" Shallow, Insulated Ceiling, Air-Tite Remodel Housing (use with 691X, 694X, 696X trims only)
		E27TAT	6" Shallow, Non-IC, Air-Tite New Construction Housing (use with 691X, 694X, 696X trims only)
		E27RTAT	6" Shallow, Non-IC, Air-Tite Remodel Housing (use with 691X, 694X, 696X trims only)



Halo LED Retrofit Enclosures

Brand	Туре	Catalog Number	Description	
Halo	Halo Retrofit ML7BXRFK		6" Retrofit Enclosure, Non-IC, BX Whip	
		ML7E26RFK	6" Retrofit Enclosure, Non-IC, E26 Screw base Interface	

Housing Compatibility - Continued

5" Trims: 591X, 592X, 593X, 594X, 595X, 596X

(Note shallow housings for use with 591X, 594X, 596X trims only)

HALO - LED Housings with LED Luminaire Connector - High-Efficacy Compliant

Brand	Housing Type	Catalog Number	Description
Halo Standard Housings H550ICAT 5" LED, Insulated Ceiling, Air-Tite, New Construction Housing		5" LED, Insulated Ceiling, Air-Tite, New Construction Housing	
		H550RICAT	5" LED, Insulated Ceiling, Air-Tite, Remodel Housing
		E550ICAT	5" LED, Insulated Ceiling, Air-Tite, New Construction Housing
		E550RICAT	5" LED, Insulated Ceiling, Air-Tite, Remodel Housing

HALO - Incandescent E26 Screwbase Housings

Brand	Housing Type	Catalog Number	Description
Halo	Standard Housings	H5ICAT	5" Insulated Ceiling, Air-Tite New Construction Housing
		H5RICAT	5" Insulated Ceiling, Air-Tite Remodel Housing
		H5ICATNB	5" Insulated Ceiling, Air-Tite New Construction Housing, No Socket Bracket
		H5T	5" Non-IC, New Construction Housing
		H5RT	5" Non-IC, Remodel Housing
		H5TNB	5" Non-IC, New Construction Housing, No Socket Bracket
		H5TM	5" Non-IC, New Construction Housing (Canada)
Halo	Shallow Housings	H25ICAT	5" Shallow, Insulated Ceiling, Air-Tite New Construction (use with 591X, 594X, 596X trims only)
		H25RICAT	5" Shallow, Insulated Ceiling, Air-Tite Remodel (use with 591X, 594X, 596X trims only)
		H25ICATNB	5" Shallow, Insulated Ceiling, Air-Tite New Construction, No Socket Bracket (use with 591X, 594X, 596X trims only)

Housings - UL Classified for Retrofit Compatibility

6" Trims: 691X, 692X, 693X, 694X, 695X, 696X

(Note shallow housings for use with 691X, 694X, 696X trims only)

Brand	Housing Type	Description
Juno	Standard Housings	IC22, IC22R, IC22W, IC22S, IC23, IC23W, TC2, TC2R, IC2
	Shallow Housings	IC21, IC21R (use with 691X, 694X, 696X trims only)
Capri	Standard Housings	CR1, PR1, QL1
	Shallow Housings	R9ASIC/PS9RM (use with 691X, 694X, 696X trims only)
Elco HL7ICA (EL7ICA)		HL7ICA (EL7ICA)
Lithonia	Standard Housings	LC6, L7X
	Shallow Housings	L7XP (use with 691X, 694X, 696X trims only)
Thomas		PS1
Commercial Electric		C7ICA, H3
Progress	Standard Housing	P87-AT †*
	Shallow Housing	P86TG (use with 691X, 694X, 696X trims only)
Lightolier		1104lCS †*, 1104lCR †*

[†] Requires replacement of torsion springs with Friction Clips. Order Friction Clip Kit separately: ML56CLIP * ML56CLIP is compatible with only baffle and reflector trims

5" Trims: 591X, 596X

Brand	Housing Type	Catalog Number
Juno	Standard Housings	IC20, IC25S, IC25W, TC20



ML56 600 Series Compliance Table

90 CRI LED Modules with ML56 Trims

	ML5606927	ML5606930	ML5606935	ML5606940
593BB	WSEC, IECC	WSEC, IECC	WSEC, IECC	WSEC, IECC
693BB	WSEC, IECC	WSEC, IECC	WSEC, IECC	WSEC, IECC
593TBZB	WSEC, IECC	WSEC, IECC	WSEC, IECC	ES, WSEC, IECC
693TBZB	WSEC, IECC	WSEC, IECC	WSEC, IECC	ES, T24, WSEC, IECC
593SNB	WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC
693SNB	T24, WSEC, IECC	T24, WSEC, IECC	T24, WSEC, IECC	ES, T24, WSEC, IECC
592H	T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC
592W	T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC
593WB	T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC	ES, T24, WSEC, IECC
592SC	ES, T24, WSEC, IECC			
692H	ES, T24, WSEC, IECC			
595WW	ES, T24, WSEC, IECC			
695WW	ES, T24, WSEC, IECC			
693WB	ES, T24, WSEC, IECC			
692SC	ES, T24, WSEC, IECC			
692W	ES, T24, WSEC, IECC			
596WB	ES, T24, WSEC, IECC			
694TBZB	ES, T24, WSEC, IECC			
594TBZB	ES, T24, WSEC, IECC			
696WB	ES, T24, WSEC, IECC			
694SNB	ES, T24, WSEC, IECC			
594SNB	ES, T24, WSEC, IECC			
694WB	ES, T24, WSEC, IECC			
594WB	ES, T24, WSEC, IECC			
594WB-30	ES, T24, WSEC, IECC			
694WB-30	ES, T24, WSEC, IECC			

Code Descriptions:

ES = ENERGY STAR® Certified Luminaire

T24 = Can be used to comply with California Title 24 High Efficacy requirements. Certified to California Title 20 Appliance Efficiency Database.

IECC = International Energy Conservation Code "High Efficacy"

WSEC = Washington State Energy Code - "High Efficacy" Luminaire

ML56 600 Series Lumen Table

90 CRI LED Modu	les with ML56 trims	l ML560	1007	l MIEG	າຕາວດ	ML560	OCO 2E	ML560	C040
	1			ML5606930					
	Trim Catalog #	Lumens	LPW	Lumens	LPW	Lumens	LPW	Lumens	LPW
)° Tilt Angle	593BB	461.1	47.9	469.5	50.9	490.5	51.1	507.6	53.8
	693BB	510.8	53.1	520.1	56.4	543.3	56.7	562.3	59.6
	593TBZB	517.8	53.8	527.3	57.1	550.8	57.4	570.0	60.4
	693TBZB	536.7	55.8	546.5	59.2	570.9	59.5	590.8	62.7
	593SNB	574.3	59.7	584.8	63.4	610.9	63.7	632.2	67.0
	693SNB	592.6	61.6	603.5	65.4	630.4	65.7	652.4	69.2
	592H	647.0	67.3	658.9	71.4	688.3	71.8	712.3	75.5
	593WB	678.7	70.6	691.1	74.9	722.0	75.3	747.2	79.2
	592SC	683.4	71.0	695.9	75.4	727.0	75.8	752.4	79.8
	592W	666.8	69.3	679.0	73.6	709.3	74.0	734.1	77.8
	595WW	687.8	71.5	700.4	75.9	731.6	76.3	757.2	80.3
	695WW	689.2	71.6	701.8	76.0	733.1	76.4	758.7	80.5
	692H	685.7	71.3	698.3	75.7	729.4	76.1	754.9	80.1
	692W	701.8	73.0	714.6	77.4	746.5	77.8	772.6	81.9
	692SC	699.7	72.7	712.5	77.2	744.3	77.6	770.3	81.7
	693WB	699.7	72.7	712.5	77.2	744.3	77.6	770.3	81.7
	596WB	715.1	74.3	728.2	78.9	760.7	79.3	787.2	83.5
	694TBZB	720.7	74.9	733.9	79.5	766.6	79.9	793.4	84.1
	696WB	727.0	75.6	740.3	80.2	773.3	80.6	800.3	84.9
	594TBZB	722.1	75.1	735.3	79.7	768.1	80.1	794.9	84.3
	694SNB	736.1	76.5	749.6	81.2	783.0	81.6	810.4	85.9
	594SNB	738.5	76.8	752.0	81.5	785.6	81.9	813.1	86.2
	694WB	760.6	79.1	774.5	83.9	809.1	84.4	837.3	88.8
	594WB	763.4	79.4	777.3	84.2	812.0	84.7	840.4	89.1
0° Tilt Angle	594WB-30	739.6	76.9	753.1	81.6	786.7	82.0	814.2	86.3
-	694WB-30	706.7	73.5	719.6	78.0	751.7	78.4	778.0	82.5

Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.



⊢СВ⊣

Photometry 5" Trims • 600 Series • 90 CRI

Multiplier Table

CCT Option	2700 K	3000 K	3500 K	4000 K
CCT Multiplier	0.91	1.00	1.03	1.08

Table based upon testing with 3000°K color temperature, 90CRI.

Multipliers may be used to determine relative lumen values with other color temperatures.

ML5606930-592SC

Test Number	P130232
Light Module	600 Series, 90CRI
Trim	5" Aperture, Specular Clear Trim
Lumens	640
Efficacy	62.7 Lm/W
SC	1.06



	_
7	
7	

	0%
D	FC
5.5	15.4
7	9.5
8	7.3
9	5.7

Cone of Light

9.5 7.2 7.2

7.3 8.4 8.4

5.7 9.4 9.4


4.6 10.4 10.4

12 3.2

5.8 5.8

12.6 12.6

Candlepower Distribution



Zonal Lumen Summary


Zone	Lumens	%Fixture
0-30	331	51.7
0-40	493	77
0-60	631	98.7
0-90	640	100
90-180	0	0
0-180	640	100


ML5606930-594WB

Test Number	P130280
Light Module	600 Series, 90CRI
Trim	5" Aperture, Directional Eyeball
Lumens	714
Efficacy	70 Lm/W
SC	1.22



Candlepower Distribution





14.3 14.6 6.9

30°			
Vertical			
Plane			
D	FC		

4' 9.7 4.5 5.2 6.9

5' 6.2 5.6 6.6 8.7

39 3'

4.3

6.7 7.8

12 1.7

)º ical ine	30) CB
FC	L	W	CB
156	1.1	1.2	1.7
39	2.2	2.6	3.5
17.3	3.3	3.8	5.2


⊢D→ ⊤

10.4

Zonal Lumen Summary

ionai Lamon Gammai y				
Zone	Lumens	%Fixture		
0-30	210	29.4		
0-40	339	47.5		
0-60	579	81		
0-90	714	100		
90-180	0	0		
0-180	714	100		

Zone	Lumens	%Fixture
0-30	210	29.4
0-40	339	47.5
0-60	579	81
0-90	714	100
90-180	0	0
0-180	714	100



Legend	
0-deg: — — — —	Wall
90-deg: ————	Side
180-deg: — — —	Room

ML5606930-595WW

P130304
600 Series, 90CRI
5" Aperture, Wall Wash with Specular Clear Trim and Specular Clear Kick Reflector
644
63.1 Lm/W
1.06



Zonal Lumen Summary

Zone	Lumens	%Fixture
0-30	316	49
0-40	475	73.8
0-60	627	97.3
0-90	644	100
90-180	0	0
0-180	644	100

Single Unit Footcandles

2.5° From Wall (Distance From Fixture Along Wall)							
DD		1'	2'	3'	4'	5'	6'
1'	2.7	1.7	0.7	0.2	0.1	0	0
2'	9.2	6.6	2.9	0.9	0.3	0.1	0
3'	10.5	8.7	4.7	1.9	0.7	0.2	0.1
4'	7.4	6.6	4.8	2.6	1.1	0.5	0.2
5'	4.9	4.6	3.7	2.5	1.4	0.7	0.3
6'	3.3	3.1	2.7	2	1.4	0.8	0.4
7'	2.3	2.2	2	1.6	1.2	0.8	0.5
8'	1.6	1.6	1.5	1.2	1	0.7	0.5
9'	1.2	1.2	1.1	1	0.8	0.6	0.5
10'	0.9	0.9	8.0	0.7	0.6	0.5	0.4

Multiple Unit Footcandles

2.5 From wall (Distance From Fixture Along Wall)							
DD		3'		4'			
1'	2.9	2.3	2.9	2.8	1.3	2.8	
2'	10.1	9.3	10.1	9.5	5.8	9.5	
3'	12.5	13.7	12.5	11.3	9.5	11.3	
4'	10.1	11.7	10.1	8.6	9.5	8.6	
5'	7.4	8.4	7.4	6.4	7.3	6.4	
6'	5.3	5.9	5.3	4.7	5.4	4.7	
7'	3.9	4.2	3.9	3.5	3.9	3.5	
8'	2.9	3.1	2.9	2.6	2.9	2.6	
9'	2.2	2.3	2.2	2	2.2	2	
10'	1.7	1.8	1.7	1.6	1.7	1.6	

Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.



Photometry 6" Trims • 600 Series • 90 CRI

Multiplier Table

CCT Option	2700 K	3000 K	3500 K	4000 K
CCT Multiplier	0.91	1.00	1.03	1.08

Table based upon testing with 3000°K color temperature, 90CRI.

Multipliers may be used to determine relative lumen values with other color temperatures.


ML5606930-692SC

Test Number	P130320
Light Module	600 Series, 90CRI
Trim	6" Aperture, Specular Clear Trim
Lumens	655
Efficacy	64.2 Lm/W
SC	0.66



Cone of Light

000						
D	FC	L	W			
5.5	25.4	3.6	3.6			
7	15.7	4.6	4.6			
8	12	5.2	5.2			
9	9.5	5.8	5.8			
10	7.7	6.6	6.6			
12	5.3	7.8	7.8			



Zonal Lumen Summary


Zone	Lumens	%Fixture
0-30	361	55.1
0-40	499	76.3
0-60	647	98.7
0-90	655	100
90-180	0	0
0-180	655	100


ML5606930-694WB

al Eyeball	



Candlepower Distribution






Zonal Lumon Summary

Zuliai Lullieli Sullillary							
Zone	Lumens	%Fixture					
0-30	210	29.5					
0-40	339	47.6					
0-60	577	81.1					
0-90	712	100					
90-180	0	0					
0-180	712	100					



PI	ane	' () -				
D	FC	L	W	СВ		
1'	155	1.1	1.2	1.7		
2'	38.8	2.2	2.6	3.5		
3'	17.2	3.3	3.8	5.2		
4'	9.7	4.5	5.2	6.9		
5'	6.2	5.6	6.6	8.7		
6'	4.3	6.7	7.8	10.4		

Candlepower Distribution



Side

Room

0-deg: 90-deg:

180-deg:

M	L560)693	30-69	5WW
_				

Test Number	P130400
Light Module	600 Series, 90CRI
Trim	6" Aperture, Wall Wash with Specular Clear Trim and Specular Clear Kick Reflector
Lumens	645
Efficacy	63.2 Lm/W
SC	0.69

Zonal Lumen Summary

Lonar Lamon Gamma,							
Zone	Lumens	%Fixture					
0-30	345	53.5					
0-40	482	74.7					
0-60	630	97.7					
0-90	645	100					
90-180	0	0					
0-180	645	100					

Single Unit Footcandles

2.5 From vvaii (Distance From Fixture Along vvaii)							
DD		1'	2'	3'	4'	5'	6'
1'	1.9	1.1	0.4	0.1	0	0	0
2'	8.5	6.1	2.6	8.0	0.2	0.1	0
3'	9	7.4	4.3	1.9	0.7	0.2	0.1
4'	6.7	5.8	4	2.3	1.1	0.5	0.2
5'	4.8	4.3	3.2	2.1	1.3	0.7	0.3
6'	3.4	3.1	2.5	1.8	1.2	8.0	0.4
7'	2.6	2.3	1.9	1.4	1	0.7	0.5
8'	2	1.8	1.5	1.2	0.9	0.6	0.5
9'	1.5	1.4	1.2	1	0.7	0.5	0.4
10'	1.2	1.1	1	8.0	0.6	0.5	0.4

Multiple Unit Footcandles

2.5' From Wall (Distance From Fixture Along Wall)

2.5 From Trull (Distance From Fixture Along Trull)						
DD	3'			4'		
1'	2	1.4	2	1.9	0.9	1.9
2'	9.3	8.4	9.3	8.7	5.2	8.7
3'	10.9	11.7	10.9	9.7	8.6	9.7
4'	9.1	9.9	9.1	7.9	8.1	7.9
5'	6.9	7.5	6.9	6.1	6.4	6.1
6'	5.2	5.6	5.2	4.6	4.9	4.6
7'	4	4.3	4	3.6	3.8	3.6
8'	3.1	3.3	3.1	2.8	3	2.8
9'	2.5	2.6	2.5	2.2	2.4	2.2
10'	2	2.1	2	1.8	1.9	1.8

Photometric tests are per IES measurement standards. Tests represent typical fixture performance. Field results may vary.