



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLG75RA 3/4 Al Insert Plug *Appleton/Oz Gedney*

Catalog Number	PLG75RA
Manufacturer	Appleton/Oz Gedney
Description	Oz-Gedney Type PLG Internal Recessed Threaded Insert Plug, Size: 3/4 In, Copper-Free Aluminum, Connection: Threaded NPT, Body Thick: 1/2 In, 1/2 In Socket Size, Third Party Certification: UL File Number E-34997 Suitable For Wet Locations, UL Liste
Weight per unit	0.0400 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

connection	Threaded NPT
Material	Copper-Free Aluminum

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4 AL INSERT PLUG
extra long description	OZG PLG75RA 3/4 IN ALUM CLOSE-UP PL
Long Description	OZ-Gedney Type PLG Internal Recessed Threaded Insert Plug, Size: 3/4 IN, Copper-Free Aluminum, Connection: Threaded NPT, Body Thick: 1/2 IN, 1/2 IN Socket Size, Third Party Certification: UL File Number E-34997 Suitable For Wet Locations, UL Liste
Product Type	3/4 In Alum Close-Up Plug
Special Features	Explosion proof, dust-ignition proof;Used to close up a tapped hole or hub

Manufacturer Information

Brand	O-Z/GEDNEY
GTIN	00783126057034
Manufacturers Part Number	PLG75RA
UPC	783126057034

Taxonomies, Classifications, and Categories

Type	Type PLG Internal Recessed Threaded Insert Plug
------	---

Packaging

Carton	50
Package	250
Weight Per each	0.04



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

For Outlet Boxes And Hubs

Third Party Certification: UL File Number E-34997 Suitable For Wet Locations, UL Listed For Hazardous Location Use As Follows: Class I, Division 1, 2, Groups A, B, C, D, Class I, Zone 1, 2, Groups IIA, IIB, IIC, Class II, Division 1, 2, Groups E, F, Glass III, CSA 009795, Applicable Third Party Standards: UL 886, CSA C22.2 Number 30, NEC Articles 500-503 & 505