

Permanent identification solutions enable reliable, comprehensive identification in harsh and industrial environments. The Panduit permanent identification system delivers long-term durability and legibility for optimum identification of pipes, conduit, cables and equipment. Featuring on-site custom marking tools, these systems offer portability for permanent identification on demand.



KEY FEATURES & BENEFITS

STAINLESS STEEL AND ALUMINUM MARKER PLATES, TAGS, AND CABLE TIES	
Broad offering of metal materials available for marker plates and cable ties:	Choose the best metal material to meet the requirements of the application
Easy feed cable tie slot:	Raised slot provides easy cable tie insertion to speed installation (available on select marker plates)
Self-locking cable tie design:	Reduces the number of installation steps required to provide lowest installed cost
Smooth cable tie cut-off:	Eliminates burrs and sharp edges after installation to protect installer and adjacent bundles
Smooth surfaces and rounded edges:	Protects the cable bundle and the installer for improved productivity, job site safety, and reliability
ON-SITE CUSTOM MARKING TOOLS	
Automatic embossing system:	The system automatically creates raised characters on stainless steel and aluminum marker plates and tags, quickly and easily using Easy-Mark™ Labeling Software, to deliver maximum visibility for applications that are exposed to dirt and paint
Metal embossing hand tool and tape system (MEHT187):	Multi-functional cutting die design creates embossed marker plates with raised cable tie slot in one step instead of three, for faster installation Lightweight and portable, easily moves from one job site to another; this system embosses 3/16" characters onto stainless steel or aluminum tape, to improve visibility in applications that are subjected to dirt or paint
Metal indenting machine:	Stable bench top tool safely indents on a wide variety of marker plates, tags, ties and straps to provide quick identification

APPLICATIONS



Cable Identification



Pipe Identification



General Mechanical Identification


Panduit Permanent Identification System

TECHNICAL INFORMATION

	Stainless Steel, Marker Plates, Tags, and Cable Ties	Aluminum Marker Plates and Cable Ties
Material:	304 and 316 Grade Stainless Steel	Aluminum – Natural and Anodized
Maximum temperature rating:	538°C (1000°F)	100°C (212°F)
Minimum temperature rating:	-80°C (-112°F)	-80°C (-112°F)
RoHS:	Compliant	Compliant
Flammability:	Non-flammable	Non-flammable
Ultraviolet light resistance:	Excellent	Good

Marker Plates and Tags

- Provides permanent identification of pipes, conduit, valves, cables, and equipment in harsh environments
- Delivers long life when exposed to chemicals, vibration, radiation, weathering, and extreme temperatures
- Available in Stainless Steel and Aluminum materials
- Designed for use with Pan-Steel® Stainless Steel Cable Ties for fast installation at lowest installed cost
- For on-site custom marking use with Panduit embossing or indenting systems



Part Number	Style	Material	Length/ Dia. In. (mm)	Width/ Dia. In. (mm)	Thickness In. (mm)	Used with Stainless Steel Cable Ties	For Use With			Std. Pkg. Qty.	Std. Cart. Qty.
							MIM	PES197	PES400		
MMP172W38-C	A	304 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S	✓			100	1000
MMP172W38-C316	A	316 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S	✓			100	1000
MMP172W38-M	A	304 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S			✓	1000	4000
MMP172-C	B	304 Stainless Steel	1.72 (44)	0.75 (19)	0.01 (0.25)	MLT-S	✓			100	1000
MMP172-M	B	304 Stainless Steel	1.72 (44)	0.75 (19)	0.01 (0.25)	MLT-S	✓		✓	1000	4000
MMP172-C316	B	316 Stainless Steel	1.72 (44)	0.75 (19)	0.01 (0.25)	MLT-S	✓			100	1000
MMP337W53-MAL-4	C	Aluminum	3.37 (85.6)	2.12 (53.8)	0.016 (0.41)	MLT-S	✓		✓	1000	4000
MMP337W71-MAL-3	D	Aluminum	3.37 (85.6)	2.12 (53.8)	0.016 (0.41)	MLT-S	✓		✓	1000	4000
MMP350W38-CQ316	E	316 Stainless Steel	3.5 (89)	0.38 (10)	0.01 (0.25)	MLT-S	✓			125	1000
MMP350W38-M	E	304 Stainless Steel	3.5 (89)	0.38 (10)	0.01 (0.25)	MLT-S		✓	✓	1000	4000
MMP350W38-M316	E	316 Stainless Steel	3.5 (89)	0.38 (10)	0.01 (0.25)	MLT-S		✓	✓	1000	4000
MMP350W38-CQ	E	304 Stainless Steel	3.5 (89)	0.38 (10)	0.01 (0.25)	MLT-S	✓			125	1000
MMP350W54-MAL	F	Aluminum	3.5 (89)	0.54 (13.7)	0.012 (0.3)	MLT-H	✓	✓	✓	1000	4000

Panduit Permanent Identification System

Marker Plates and Tags (Continued)




Part Number	Style	Material	Length/ Dia. In. (mm)	Width/ Dia. In. (mm)	Thickness In. (mm)	Used with Stainless Steel Cable Ties	For Use With			Std. Pkg. Qty.	Std. Cart. Qty.
							MIM	PES197	PES400		
MMP350-C	G	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-S	✓			100	1000
MMP350-C316	G	316 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-S	✓			100	1000
MMP350-M	G	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-S	✓	✓	✓	1000	4000
MMP350-M316	G	316 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-S	✓	✓	✓	1000	4000
MMP350H-C	I	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓			100	1000
MMP350H-C316	I	316 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓			100	1000
MMP350H-M	I	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓	✓	✓	1000	4000
MMP350H-M316	I	316 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓	✓	✓	1000	4000
MMP350H-MAL	I	Aluminum	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓	✓	✓	1000	4000
MMP350W17-Q	J	304 Stainless Steel	3.5 (89)	1.73 (44)	0.015 (0.4)	MLT-S	✓		✓	25	250
MMP350W17-Q-M	J	304 Stainless Steel	3.5 (89)	1.73 (44)	0.015 (0.38)	MLT-S	✓		✓	1000	4000
MT172W38-M	L	304 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-H			✓	1000	4000
MT172-C	M	304 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S	✓			100	1000
MT172-C316	M	316 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S	✓			100	1000
MT172-M	M	304 Stainless Steel	1.72 (44)	0.38 (10)	0.01 (0.25)	MLT-S	✓		✓	1000	4000
MT206W119A-Q	N	304 Stainless Steel	2.06 (52)	1.19 (30)	0.015 (0.38)	MLT-H	✓			25	250
MT350W38-M316	O	316 Stainless Steel	3.5 (89)	0.38 (10)	0.01 (0.25)	MLT-S			✓	1000	4000
MT350-C	P	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓			100	1000
MT350-C316	P	316 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓			100	1000
MT350-M	P	304 Stainless Steel	3.5 (89)	0.75 (19)	0.01 (0.25)	MLT-H	✓		✓	1000	4000
MT350W17-Q	Q	304 Stainless Steel	3.5 (89)	1.73 (44)	0.015 (0.38)	MLT-S	✓			25	250
MT350W17-D-4HL	Q	304 Stainless Steel	3.5 (89)	1.73 (44)	0.015 (0.38)	MLT-S	✓		✓	500	500
MT350W17-Q-M	Q	304 Stainless Steel	3.5 (89)	1.73 (44)	0.015 (0.38)	MLT-S	✓		✓	1000	4000
CIRCULAR TAGS											
MT1D-Q	R	304 Stainless Steel	–	1 (25)	0.035 (0.89)	MLT-H	✓			25	250
MT150D-Q	R	304 Stainless Steel	–	1.5 (38)	0.035 (0.89)	MLT-S	✓			25	250


Panduit Permanent Identification System

Panduit Embossing System*

- To deliver a permanent identification solution on-site and on demand when it's needed
- Creates raised characters on stainless steel and aluminum marker plates, to deliver maximum visibility for medium to high volume applications that are exposed to dirt and paint
- Fast embossing speed of up to 300 plates per hour
- Includes both 3 mm and 5 mm characters
- Compatible with numerous sizes and styles of metal plates and tags
- Input hopper allows for easy stacking of plates, saving time and money
- Output hopper keeps plates neatly stacked in the order that they are embossed
- Easy-Mark™ Labeling Software included. Software allows for a quick print legend and exact preview, saving time and reducing print costs



5 mm font on MMP350-M



3 mm font on MT350W17-Q-M

Part Number	Description	Std. Pkg. Qty.
PES400	Panduit Embossing System, 0.188 in. (5mm) and 0.118 in. (3mm) characters, 35.8 in. x 23.6 in. x 16.5 in., 154lbs. (75kg), 100 to 240 VAC, 50/60Hz	1

Characters include: ABCD...Z, 0123...9, @ # % & * () - + : , . / ' "

*For use with 1000 pack marker plates only.

Easy-Mark™ Desktop Labeling Software


- Powerful, easy-to-use, and affordable software that provides innovative features and functionality to address unique labeling needs
- Quickly create simple or complex labels with text boxes, lines, frames, or tables, and other useful tools
- Marker plate formats for use with PES400 are included
- Design detailed labels with multiple zones and objects for applications such as rating plates, arc flash labels, and fiber optic enclosures
- Upgrades available at panduit.com

System Requirements:

- 4 GB hard drive space and 4 GB Memory
- Microsoft Windows 10 or higher (64 bit)
- Microsoft .NET Framework 4.8 or higher
- Mouse or compatible pointing device
- Keyboard
- For EM-DL downloadable version: Internet connection
- For EM-2GO version: USB Port

Note: Additional requirements for Server version only:

- Windows Server 2016 (64 bit) or higher
- 8 GB hard drive space and 32 GB Memory



Part Number	Description
EM-DL*	Easy-Mark Desktop Labeling Software - Downloadable Version
EM-2GO	Easy-Mark Desktop Labeling Software - USB Flash Drive Version
EM-SERVER-DL*	Easy-Mark Desktop Labeling Software - Server Version - Downloadable
EM-SERVER-USB	Easy-Mark Desktop Labeling Software - Server Version - USB Flash Drive

Windows is a registered trademark of Microsoft Corp. in the United States and/or other countries.

*Customer will receive a DVD case with information and serial number for the downloadable version.

Panduit Permanent Identification System

Metal Embossing Hand Tool and Tape System

- Multi-functional cutting die design creates embossed marker plates with raised cable tie slot in one step instead of three, for faster installation
- Lightweight, compact and portable, allows user to create custom length identification on demand at remote job sites
- Embosses 3/16" characters onto stainless steel or aluminum tape, to improve visibility in applications that are subjected to dirt or paint




Part Number	Description	Std. Pkg. Qty.
TOOL KIT		
MEHT187	Includes tool, additional marking wheel, carrying case, one roll each META (aluminum) and METS (stainless steel) tape. Characters included: A B C D E F G H I J K L M N O P Q R S T U V W X Y Z 1 2 3 4 5 6 7 8 9 / ()	1
TM26319B01	Embossing Wheel Replacement Kit	
TM26971B01	Gray Embossing Wheel Service Assembly	
TAPE		
META-X	0.50" x 16' (12.7mm x 4.9m) aluminum tape*.	10
METS3-X	0.50" x 21' (12.7mm x 6.4m) 316 grade stainless steel tape.	
METS4-X	.50" x 21' (12.7mm x 6.4m) 304 grade stainless steel tape.	

*Aluminum ties are recommended for use with aluminum tape to prevent galvanic reaction (corrosion that can occur between stainless steel and aluminum in certain environments).

Metal Indenting Machine

- Provides quick, easy, and permanent identification with aluminum marker plates and cable ties and stainless steel marker plates, tags, cable ties and straps for low to medium volume applications
- Automatic table indexing advances material forward for convenience and improved productivity
- Aluminum base for tool stability and durable construction



Part Number	Description	Std. Pkg. Qty.
INDENTING MACHINE		
MIM094	Indenting machine with 3/32" (2.38mm) character wheel, 11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg).	1
MIM125	Indenting machine with 1/8" (3.18mm) character wheel, 11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg).	
MIM187	Indenting machine with 3/16" (4.77mm) character wheel, 11.25" (286mm) x 16.25" (413mm) x 11.75" (298mm), 41 lbs. (18.6 kg).	
INTERCHANGABLE WHEEL KITS		
MIW094	3/32" (2.38mm) character wheel kit (wheel and indexing gear).	1
MIW125	1/8" (3.18mm) character wheel kit (wheel and indexing gear).	
MIW187	3/16" (4.77mm) character wheel kit (wheel and indexing gear).	

Characters include: ABC...Z, 0123...9, & / @ '-

Panduit Permanent Identification System

Pan-Steel® Stainless Steel Cable Ties

- Delivers strength, long life, and resistance to chemicals, vibration, radiation, weathering and extreme temperatures
- Use with Pan-Steel® Marker Plates and Tags for fast installation at the lowest installed cost
- Smooth surfaces and rounded edges, protects the cable bundle and the installer for improved productivity, job site safety, and reliability
- Patented self-locking head reduces installation steps for improved productivity



MLTS



MLTH

Part Number	Max. Bundle Diameter In. (mm)	Length* In. (mm)	Min. Loop Tensile Strength** Lbs. (N)	Min. Bundle Diameter In. (mm)	Width In. (mm)	Thickness In. (mm)	Recommended Panduit Installation Tool	Std. Pkg. Qty.	Std. Cart. Qty.
-------------	-------------------------------	------------------	---------------------------------------	-------------------------------	----------------	--------------------	---------------------------------------	----------------	-----------------

AIISI 304 STAINLESS STEEL – FOR GENERAL PURPOSE

STANDARD CROSS SECTION

MLT1S-CP	1.0 (25)	5.0 (127)	200 (890)	0.50 (12.7)	0.18 (4.6)	0.01 (0.25)	GS4MT-E, HTMT, ST2MT	100	500
MLT2S-CP	2.0 (51)	7.9 (201)							
MLT4S-CP	4.0 (102)	14.3 (362)							
MLT6S-CP	6.0 (152)	20.5 (521)							

HEAVY CROSS SECTION

MLT2H-LP	2.0 (51)	7.9 (201)	450 (2000)	0.50 (12.7)	0.31 (7.9)	0.01 (0.25)	PBTMT(/E), GS4MT-E, HTMT, ST2MT	50	250
MLT4H-LP	4.0 (102)	14.3 (362)							
MLT6H-LP	6.0 (152)	20.5 (521)							

AIISI 316 STAINLESS STEEL – FOR SUPERIOR CORROSION RESISTANCE

STANDARD CROSS SECTION

MLT1S-CP316	1.0 (25)	5.0 (127)	200 (890)	0.50 (12.7)	0.18 (4.6)	0.01 (0.25)	GS4MT-E, HTMT, ST2MT	100	500
MLT2S-CP316	2.0 (51)	7.9 (201)							
MLT4S-CP316	4.0 (102)	14.3 (362)							
MLT6S-CP316	6.0 (152)	20.5 (521)							

HEAVY CROSS SECTION

MLT2H-LP316	2.0 (51)	7.9 (201)	450 (2000)	0.50 (12.7)	0.31 (7.9)	0.01 (0.25)	PBTMT(/E), GS4MT-E, HTMT, ST2MT	50	250
MLT4H-LP316	4.0 (102)	14.3 (362)							
MLT6H-LP316	6.0 (152)	20.5 (521)							

*Other lengths available, contact customer service.

**Tested per SAE Standard AS23190/3 (formerly MIL).

^Order number of pieces required, in multiples of Standard Package Quantity.

See pages 6 and 7 for stainless steel and brass marker plates and tags.

Panduit Permanent Identification System

Cable Tie Installation Tools

- Tools speed installation
- Feature high reliability, low maintenance, long life
- GS4MT-E and PBTMT feature automatic tension and cut-off capabilities for improved productivity and installer safety

Part Number	Description	Std. Pkg. Qty.
HIGH VOLUME USE		
PBTMT	Battery powered installation tool, for use with Pan-Steel® Heavy, Extra-Heavy, and Super-Heavy Cross Section MLT Style Ties, and MLTD Double Wrapped Style Ties, 2 – 12 volt lithium-ion batteries and 115 volt, 60 Hz charger included.	1
MEDIUM VOLUME USE		
ST2MT	Used with Standard and Heavy Cross Section Pan-Steel® Type MLT Ties.	1
GS4MT-E	Used with Heavy Cross Section Pan-Alum™ Type MLT Ties and Standard and Heavy Cross Section Pan-Steel® Type MLT Ties.	1



PBTMT



ST2MT



GS4MT-E