ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX34AA023F00 Mmax 3P 480V In/3P 480V Out 23A 15HP FS4 W Emc & 5

Eaton Corp

Catalog Number	MMX34AA023F00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Adjustable Frequency Drive Full Version AA Software Design Series FS4 Frame 380–480V 3-Phase In 460V Three-Phase Out IP20 Enclosure Rating 15 HP 23A Output Current 23A Nomincal Ac Current
Weight per unit	12.5 (lbs/each)
Product Category	Ac Drives

Features

dimensions	6.5000 IN X 6.6100 IN X 14.5700 IN
Number of Phases	Three-phase

Descriptions

Description	MMAX 3P 480V IN/3P 480V OUT 23A 15HP FS4 W EMC & 5
extra long description	ETN MMX34AA023F0-0 MMX 480V 23A,15H
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series Adjustable Frequency Drive Full version AA software design series FS4 frame 380–480V 3-phase in 460V three-phase out IP20 enclosure rating 15 hp 23A Output current 23A Nomincal AC current
Product Type	MMX 480V 23A, 15HP, FS4, W Emc&5% Choke

Manufacturer Information

Brand	Eaton
GTIN	00786685626666
Manufacturers Part Number	MMX34AA023F00
UPC	786685626666

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Availability

Status	Inactive

Packaging

Carton	1
Weight Per each	12.5

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
standard	EN 61800-3,EN 61800-5-1,EN 60204-1,IEC Rated,cUL Listed,UL Listed,RoHS Compliant,EMC Category C2, C3, and C4 (Level H): With an internal RFI filter option,C-Tick Compliant,CE Marked