



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **MMX34AA5D6F00 M-Max 3P 480V In/3P 480V Out 5.6A 3.0HP FS2 W Emc** *Eaton Corp*

Catalog Number	MMX34AA5D6F00
Manufacturer	Eaton Corp
Description	M-Max Series Drive, FS2 Frame, 3 (Input);3 (Output) Phases, 380 to 480 V;460 V, 7.3 A, 5.6 A, 1.54 LB
Weight per unit	3.0 (lbs/each)
Product Category	Ac Drives

### **Features**

dimensions	3.5400 IN X 7.6800 IN X 4.0000 IN
Output Current	5.6 A

### **Descriptions**

Description	M-MAX 3P 480V IN/3P 480V OUT 5.6A 3.0HP FS2 W EMC
extra long description	ETN MMX34AA5D6F0-0 MMX 480V,5.6A,3.
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.

### **Manufacturer Information**

Brand	EATON CUTLER-HAMMER
GTIN	00786685268828
UPC	786685268828

### **Taxonomies, Classifications, and Categories**

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

### **Packaging**

Carton	1
Weight Per each	3

### **Uses, Certifications, and Standards**

Application	OtherElec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
standard	UL Listed,cUL Certified,EN 60204-1,EN 61800-3,EN 61800-5-1,C-Tick Compliant,RoHS Compliant,CE Marked,EMC Category C2, C3, and C4 (Level H): With an internal RFI filter option