



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000



PN1410LFM 16-14AWG #10STD Nylon Insld Fork TRML *Panduit Corporation*

Catalog Number	PN1410LFM
Manufacturer	Panduit Corporation
Description	Locking Fork Terminal, Nylon Insulated, 16 - 14 Awg, #10 Stud Size, Bulk Package.
Weight per unit	0.0025 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
insulation	Nylon
Material	Copper
Voltage Rating	600
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#10
------	-----

Descriptions

Description	16-14AWG #10STD NYLON INSLTD FORK TRML
extra long description	PAN PN14-10LF-M Pan-Term® PN14-10LF
Long Description	Locking Fork Terminal, nylon insulated, 16 - 14 AWG, #10 stud size, bulk package.
Product Type	Pan-Term® PN14-10LF-M Loose Piece Forks

Manufacturer Information

Brand	Panduit®
GTIN	00074983800971
Manufacturers Part Number	PN14-10LF-M
UPC	074983800971

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Locking Fork Terminal

Availability

minimum qty	1000
-------------	------

Packaging

Carton	1000
Weight Per each	0.0025



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8110 Anderson Road Suite 100
33634-0000, FL Tampa
Phone: 813-934-6264
Fax: 000-000-0000

Uses, Certifications, and Standards

Enclosure	Fork shape
Mounting	7/32
standard	CSA Certified LR31212;UL Listed 587H E52164
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)