



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PPKG1PWH 300W RF Plug-In/Remote White *Lutron*

Catalog Number	PPKG1PWH
Manufacturer	Lutron
Description	Lutron Caseta Wireless Single-Pole/3-Way Smart Lighting Lamp Dimmer and Remote Kit, White
Weight per unit	0.4500 (lbs/each)
Product Category	Lighting Dimmers

### Features

media	Yes
Voltage Rating	120

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Size	3.13 x 3.19; 79.4 x 55.6
------	--------------------------

### Descriptions

Description	300W RF PLUG-IN/REMOTE WHITE
extra long description	LUT P-PKG1P-WH Caseta Lamp Dimmer a
Features	Conveniently create just the right light for reading, watching TV or entertaining, with the Lutron Caseta Wireless plug-in lamp dimmer and Pico smart remote control. The plug-in lamp dimmer simply plugs into a standard outlet and can be used with up to 2 lamps. Control the lights from anywhere in the room by using the Pico remote control either in your hand, on a tabletop pedestal (sold separately) or by mounting the remote directly to the wall. You can even add a wall switch to control plug-in lamps witho
Long Description	Lutron Caseta Wireless Single-Pole/3-Way Smart Lighting Lamp Dimmer and Remote Kit, White
Product Type	Caseta Lamp Dimmer and Remote Kit

### Manufacturer Information

Brand	Lutron
GTIN	00784276072083
Manufacturers Part Number	P-PKG1P-WH
UPC	784276072083

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
----------------------	--------------------------------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.45

## Uses, Certifications, and Standards

Application	Lighting Control
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	50 to 60
Operating Temperature	32 to 104
standard	cULus Listed, NOM Certified