

Specifications

Eaton PRL2X3600X42C

Eaton PRL2X INTERIOR FOR TFL 480/277 3P
4W 600A 42 CKT CU BUS



General specifications

PRODUCT NAME	Eaton Pow-R-Xpress PRL2X panelboard
CATALOG NUMBER	PRL2X3600X42C
UPC	786689363383
PRODUCT LENGTH/DEPTH	61 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	123 lb
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL 67

Physical Attributes

BUS MATERIAL	Copper
NUMBER OF CIRCUITS	42
TYPE	PRL2X INTERIOR

Performance Ratings

AMPERAGE RATING	600A
-----------------	------

Resources

BROCHURES	Pow-R-Xpress stocking program flyer
	Pow-R-Xpress quick selector reference guide
	Eaton's Pow-R-Xpress stocking program
MULTIMEDIA	Pow-R-Line Xpert family overview
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PRL2X3600X42C

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton PRL2X3600X42C

Eaton PRL2X INTERIOR FOR TFL 480/277 3P
4W 600A 42 CKT CU BUS



General specifications

PRODUCT NAME	Eaton Pow-R-Xpress PRL2X panelboard
CATALOG NUMBER	PRL2X3600X42C
UPC	786689363383
PRODUCT LENGTH/DEPTH	61 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	123 lb
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL 67

Physical Attributes

BUS MATERIAL	Copper
NUMBER OF CIRCUITS	42
TYPE	PRL2X INTERIOR

Performance Ratings

AMPERAGE RATING	600A
-----------------	------

Resources

BROCHURES	Pow-R-Xpress stocking program flyer
	Pow-R-Xpress quick selector reference guide
	Eaton's Pow-R-Xpress stocking program
MULTIMEDIA	Pow-R-Line Xpert family overview
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PRL2X3600X42C

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

