





GE
Lighting

12590 - MVR70/U/MED

GE Multi-Vapor® PulseArc® Quartz Metal Halide BD17



CAUTIONS & WARNINGS

R- WARNING: This lamp can cause serious skin burn and eye inflammation from shortwave ultraviolet radiation if outer envelope of the lamp is broken or punctured, and the arc tube continues to operate. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain types of lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available. Visit the FDA website for more information: <http://www.fda.gov/cdrh/radhealth/products/urburns.html>

Caution

- Lamp may shatter and cause injury if broken
 - Dispose of lamp in a closed container.
 - Do not use excessive force when installing lamp.
 - Do not use lamp if outer glass is scratched or broken.

Warning

- A damaged lamp emits UV radiation which may cause eye/skin injury
 - Turn power off if glass bulb is broken. Remove and dispose of lamp.
- Risk of Burn
 - Allow lamp to cool before handling.
 - Do not turn on lamp until fully installed.
- Risk of Electric Shock
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.
 - Turn power off before inspection, installation or removal.
- Risk of Fire
 - Keep combustible materials away from lamp.
 - Use in fixture rated for this product.
- Unexpected lamp rupture may cause injury, fire, or property damage
 - Do not exceed rated voltage.
 - Do not turn on lamp until fully installed.
 - Do not use beyond rated life.
 - Do not use lamp if outer glass is scratched or broken.
 - Do not use where directly exposed to water or outdoors without an enclosed fixture.
 - Turn lamp off at least once for 15 minutes per week.
 - Use in enclosed fixture rated for this product.
 - Use only properly rated ballast.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution

GENERAL CHARACTERISTICS

Lamp Type	High Intensity Discharge - Quartz Metal Halide
Bulb	BD17
Base	Medium Screw (E26)
Bulb Finish	Clear
Rated Life	12000.0 hrs
Bulb Material	Hard glass
Lamp Enclosure Type (LET)	Enclosed fixtures only
LEED-EB MR Credit	136 picograms Hg per mean lumen hour

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	5500.0
Mean Lumens	2900.0
Nominal Initial Lumens per Watt	78
Color Temperature	4000.0 K
Color Rendering Index (CRI)	65.0
Effective Arc Length	0.33 in

ELECTRICAL CHARACTERISTICS

Wattage	70.0
Voltage	85.0
Burn Position	Universal burning position
Open Circuit Voltage (peak lead ballast) (MIN)	332.0 V
Open Circuit Voltage (RMS lag ballast) (MIN)	235.0 V
Warm Up Time to 90% (MIN)	2.0 min
Warm Up Time to 90% (MAX)	5.0 min
Hot Restart Time to 90% (MIN)	10.0 min
Hot Restart Time to 90% (MAX)	15.0 min

DIMENSIONS

Maximum Overall Length (MOL)	5.4300 in(137.9 mm)
Nominal Length	5.430 in(137.9 mm)
Bulb Diameter (DIA)	2.125 in(54.0 mm)
Light Center Length (LCL)	3.430 in(87.1 mm)

PRODUCT INFORMATION

Product Code	12590
Description	MVR70/U/MED
ANSI Code	M98
Standard Package	Case
Standard Package GTIN	10043168125908
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168125901

